

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0639007600](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: FineAdjust Applicator for 2.00mm Crimp Terminal, AWG 22-28

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family [Application Tooling](#)
Series [207127](#)
Comments See Tooling Specification (PDF) Above, Terminals will accommodate the UL1007 wires

Function [Crimp](#)
Geographic Area [Global](#)
Level of Automation [Automatic, Semi-Automatic](#)
More Detailed Tech Information [applicationtooling@molex.com](#)
Overview [Application Tooling](#)
Product Name [FineAdjust](#)
Tool Type [Applicator](#)
UPC [883906195717](#)
Warranty Disclaimer [CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors \("Molex Tooling"\). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.](#)

Physical
Net Weight [4983.259/g](#)

Material Info

Reference - Drawing Numbers
[Application Tooling Documents](#)

[ATS-639007600-001](#), [TM-638000029-001](#),
[TM-638000029CN-001](#), [TM-638000029DE-001](#),
[TM-638000029FR-001](#), [TM-638000029IT-001](#),
[TM-638000029JP-001](#), [TM-638000029KR-001](#),
[TM-638000029MY-001](#), [TM-638000029PL-001](#),
[TM-638000029RU-001](#), [TM-638000029SK-001](#),
[TM-638000029SP-001](#), [TM-638000029TH-001](#),
[TM-638000029TW-001](#), [TM-638000029VN-001](#),
[TM-638004900-001](#), [TM-638004900CN-001](#),
[TM-638004900SP-001](#)



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Not Reviewed
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Relevant
For more information, please visit [Contact US](#)

China ROHS Not Relevant
ELV Not Relevant
RoHS Phthalates Not Reviewed

Search Parts in this Series
[207127](#) Series

Use With
Molex TM-3000: [638017200](#) , [638017300](#)
 , Molex TM-4000: [638017600](#) , Molex
TM-2000: [638008300](#) , [638008400](#) , and
Most Industry Standard Presses or Wire
Process Machines

Application Tooling Description	FAQ Product #
2.00mm Pitch Crimp Terminal 56086, Male, 22-28 AWG, Reel, for 51227 Housing	560868000
2.00mm Pitch Crimp Terminal, Female, 22-28 AWG, Reel	593708000

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63900-7600](#)