

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0639038400
Status: Active
Overview: Application Tooling
Description: FineAdjust Applicator for Male and Female Terminal Ditto Interconnects, 20-22 AWG

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Application Tooling
Series	207127
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Ditto, FineAdjust
Tool Type	Applicator
UPC	889056287449
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers
Application Tooling Documents ATS-639038400-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	
Not Relevant	
REACH SVHC	
Not Relevant	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Relevant

Search Parts in this Series
[207127](#) Series

Use With
Molex TM-3000: [638017200](#) , [638017300](#)
 , Molex TM-4000: [638017600](#) , Molex
TM-2000: [638008300](#) , [638008400](#) , and
Most Industry Standard Presses or Wire
Process Machines

Application Tooling Description	FAQ Product #
Ditto Hermaphroditic Crimp Terminal, Tin Brass, Preplated Tin, 20-22 AWG	1502000001
Ditto Hermaphroditic Crimp Terminal, Copper Nickel, Select Gold Plating, 20-22 AWG, for High-Temperature (-40° to +150°C) Housing	1502000011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

63903-8400