

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0639041400

Status:

Active

Overview:

Application Tooling

Description:

FineAdjust Applicator for Mini-Fit Jr., Mini-Fit HCS, and Mini-Fit Plus HCS Crimp Terminals, 16 AWG with Large Insulation Diameters

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207127
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	FineAdjust, Mini-Fit HCS, Mini-Fit Jr., Mini-Fit Plus HCS
Tool Type	Applicator
UPC	889056528917
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-639041400-001



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207127 Series

Use With

Molex TM-3000: 638017200 , 638017300 , Molex TM-4000: 638017600 , Molex TM-2000: 638008300 , 638008400 , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
Mini-Fit Female Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass, 16, 18+22, 20+20, 20+22 AWG, Reel	39000077
Mini-Fit Female Crimp Terminal, Tin (Sn) over Phosphor Bronze, 16, 18+22, 20+20, 20+22 AWG, Reel	39000079
Mini-Fit Male Crimp Terminal, Tin (Sn) over Copper Plated	39000081

Brass, 16, 18+22,
20+20, 20+22 AWG,
Reel
Mini-Fit Male Crimp 39000083
Terminal, Tin (Sn)
over Phosphor
Bronze, 16, 18+22,
20+20, 20+22 AWG,
Reel
Mini-Fit Female 39000089
Crimp Terminal, Gold
(Au) over Brass, 16
AWG, Reel
Mini-Fit Male Crimp 39000095
Terminal, Selective
Gold (Au) and
Selective Tin (Sn)
over Nickel (Ni), 16
AWG, Reel
Mini-Fit Male Crimp 39000124
Terminal, Tin
(Sn) Plated Brass
Contact, 16 AWG,
Reel
Mini-Fit Male Crimp 39000130
Terminal, Tin (Sn),
Phosphor Bronze, 16
AWG, Reel
Mini-Fit Female 39000185
Crimp Terminal,
Selective Gold (Au)
over Phosphor
Bronze, 16 AWG,
Reel
Mini-Fit Female 39000211
Crimp Terminal, Tin
(Sn) over Nickel (Ni),
16 AWG, Reel
Mini-Fit Female 39000217
Crimp Terminal, Tin
(Sn) over Phosphor
Bronze, 16 AWG,
Reel
Mini-Fit Male Crimp 39000223
Terminal, Phosphor
Bronze, Gold (Au),
16 AWG, Reel
Mini-Fit Plus Crimp 457503111
Terminal, 16 AWG,
Reel, Copper (Cu)
Alloy, Tin (Sn)
Mini-Fit Plus Crimp 457503211
Terminal, 16 AWG,
Reel, Copper (Cu)
Alloy, Gold (Au)
Selective
Mini-Fit Plus Crimp 460123141
Terminal, 16 AWG,
Reel, Tin (Sn) Plating
Mini-Fit Plus 460123151
Grounding Crimp
Terminal, 16 AWG,
Reel, Tin (Sn) Plating
Mini-Fit Plus Crimp 460123241
Terminal, 16 AWG,

Reel, 0.76µm
Selective Gold (Au)
Plating
Mini-Fit Plus 460123251
Grounding Crimp
Terminal, 16 AWG,
Reel, 0.76µm
Selective Gold (Au)
Plating
Mini-Fit Plus High 460183541
Mating Cycle Female
Crimp Terminal, 16
AWG, Reel, Select
Gold (Au) Plating
with Proprietary
Molex Advanced
Contact Surface
Finish (CSF) in
Contact Area

This document was generated on 10/07/2021
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

63904-1400