

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0714781003

Status:

Active

Overview:

LFH™ Interconnect System

Description:

1.27mm Pitch LFH™ Matrix 50 Receptacle, Shielded, 80 Circuits, Vertical, 80 Circuits

Documents:

3D Model

Drawing (PDF)

Product Specification PS-70928-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

General

Product Family

Series

Application

Component Type

Overview

Product Name

Type

UPC

I/O Connectors

71478

Board-to-Board, Wire-to-Board

Receptacle

LFH™ Interconnect System

LFH™

N/A

800754871150

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Flammability

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Orientation

PC Tail Length

PCB Retention

PCB Thickness - Recommended

Packaging Type

Panel Mount

Pitch - Mating Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

Wire Size AWG

80

80

Black

94V-0

Yes

Beryllium Copper

Gold

Tin

High Temperature Thermoplastic

Vertical

4.70mm

None

1.60mm

Tube

Yes

1.27mm

0.762µm

2.540µm

Yes

Yes

-20°C to +80°C

Surface Mount

N/A

Electrical

Current - Maximum per Contact

Shielded

Voltage - Maximum

1.0A

Yes

40V

Material Info

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-70928-001

SDA-71478-100*



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[71478](#) Series

Mates With

[71475](#) , [71720](#) , [717477](#)

Use With

[71628](#) Guide Pin, [70982](#) Hex Screw Kit, Guide Sleeve [71629](#) or [71770](#)

This document was generated on 12/07/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[71478-1003](#)