

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0747630010

Status:

Active

Overview:

zQSFP+ and QSFP+ Integrated Product Solutions

Description:

QSFP+ Universal Loopback Adapter, 100 Ohms Impedance, Serial ID, 0dB



Series image - Reference only

|                               |                                                      |
|-------------------------------|------------------------------------------------------|
| Documents:                    |                                                      |
| <a href="#">Drawing (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a> |
| Agency Certification          |                                                      |
| UL                            | E107635                                              |
| General                       |                                                      |
| Product Family                | I/O Connectors                                       |
| Series                        | 74763                                                |
| Application                   | Module-to-Board                                      |
| Component Type                | Adapter                                              |
| Overview                      | zQSFP+ and QSFP+ Integrated Product Solutions        |
| Product Name                  | QSFP Plus, QSFP+                                     |
| Type                          | N/A                                                  |
| UPC                           | 883906054281                                         |
| Physical                      |                                                      |
| Boot Color                    | N/A                                                  |
| Circuits (Loaded)             | N/A                                                  |
| Color - Resin                 | Blue (Light)                                         |
| Flammability                  | 94V-0                                                |
| Gender                        | Dual                                                 |
| Lock to Mating Part           | No                                                   |
| Material - Plating Mating     | Nickel                                               |
| Net Weight                    | 2.000/g                                              |
| Orientation                   | Horizontal                                           |
| Packaging Type                | Tray                                                 |
| Panel Mount                   | No                                                   |
| Pitch - Mating Interface      | N/A                                                  |
| Polarized to Mating Part      | No                                                   |
| Termination Interface: Style  | Through Hole                                         |
| Electrical                    |                                                      |
| Current - Maximum per Contact | N/A                                                  |
| Shielded                      | No                                                   |
| Voltage - Maximum             | 3.3V                                                 |
| Material Info                 |                                                      |

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

74763 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[74763-0010](#)