

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0747630025

Status:

Active

Overview:

zQSFP+ and QSFP+ Integrated Product Solutions

Description:

QSFP+ Universal Loopback Adapter, 100 Ohms Impedance, Serial ID, 5dB, 12C Port Expander



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

|                               |                                               |
|-------------------------------|-----------------------------------------------|
| Agency Certification          |                                               |
| UL                            | E107635                                       |
| General                       |                                               |
| Product Family                | I/O Connectors                                |
| Series                        | 74763                                         |
| Application                   | Module-to-Board                               |
| Component Type                | Adapter                                       |
| Overview                      | zQSFP+ and QSFP+ Integrated Product Solutions |
| Product Name                  | QSFP Plus, QSFP+                              |
| Type                          | N/A                                           |
| UPC                           | 800756931807                                  |
| Physical                      |                                               |
| Boot Color                    | N/A                                           |
| Circuits (Loaded)             | N/A                                           |
| Color - Resin                 | Light Green                                   |
| Flammability                  | 94V-0                                         |
| Gender                        | Dual                                          |
| Lock to Mating Part           | No                                            |
| Material - Plating Mating     | Nickel                                        |
| Net Weight                    | 33.204/g                                      |
| Orientation                   | Horizontal                                    |
| Packaging Type                | Tray                                          |
| Panel Mount                   | No                                            |
| Pitch - Mating Interface      | N/A                                           |
| Polarized to Mating Part      | No                                            |
| Termination Interface: Style  | Through Hole                                  |
| Electrical                    |                                               |
| Current - Maximum per Contact | N/A                                           |
| Shielded                      | No                                            |
| Voltage - Maximum             | 3.3V                                          |
| Material Info                 |                                               |

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

|                 |               |
|-----------------|---------------|
| China ROHS      | Green Image   |
| ELV             | Not Relevant  |
| RoHS Phthalates | Not Contained |

Search Parts in this Series  
74763 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[74763-0025](#)