

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0752350107

Status:

Active

Overview:

GbX Backplane Connector System

Description:

GbX 4 Pair Backplane Connector System, Open Header, 80 Circuits, 10 Columns, Gold (Au) 1.27µm, Pin Length 3.55mm

Documents:

Drawing (PDF)

Product Specification PS-75221-999-001 (PDF)

Packaging Specification PK-70873-563 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Application Tooling Documents

Comments

Component Type

Overview

Product Name

UPC

Backplane Connectors

75235

Backplane

TM-622022099

Open Header, Open Header

PCB Header

GbX Backplane Connector System

GbX

822350173612

Physical

Circuits (Loaded)

Circuits (maximum)

Durability (mating cycles max)

First Mate / Last Break

Flammability

Guide to Mating Part

Keying to Mating Part

Material - Plating Mating

Net Weight

Number of Columns

Number of Pairs

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to PCB

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

80

80

200

No

94V-0

No

None

Gold

4.568/g

10

4

8

Vertical

2.30mm

No

Yes

1.60mm

Tray

1.85mm

1.85mm

No

Yes

Yes

105°C

Electrical

Current - Maximum per Contact

Data Rate

Real Signals (per 25mm)

Shield Type

Shielded

Voltage - Maximum

1.0A


8.0 Gbps

108

Ground Plane Shield

Yes

120V AC (RMS)/DC



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China RoHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

75235 Series

Mates With

75220 GbX Daughtercard

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Insertion Tool, 4-Pair by 10-Wide

622022000

Insertion Tool, 4-pair by 20-Wide

622022010

Single Pin Repair Tool

622022090

Shield Removal Tool

622022100

Solder Process Data

Lead-free	Process Capability	N/A
-----------	--------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-70873-563
Product Specification	PS-75221-999-001
Sales Drawing	SD-75235-010

This document was generated on 09/16/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[75235-0107](#)