

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0781091001

Status:


Active

Overview:

Serial ATA Connectors

Description:

1.27mm Pitch Micro Serial ATA Device Receptacle for 45.72mm HDD/SSD, Right-Angle, Surface Mount, Mid-Mount, 14 Circuits, Lead-Free



Series image - Reference only

Documents:	
3D Model	Product Specification PS-78109-001-001 (PDF)
Drawing (PDF)	Packaging Specification PK-78109-100-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Receptacles
Series	78109
Application	Board-to-Board, Signal
Comments	Without Optional Manufacturing Pins (S1 to S7, P1 to P7)
Electrical Model	Yes
Overview	Serial ATA Connectors
Product Name	Micro Serial ATA, Serial ATA
UPC	884982032996
Physical	
Circuits (Loaded)	14
Circuits (maximum)	14
Color - Resin	Black
Durability (mating cycles max)	500
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Number of Rows	1
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
Packaging Type	Tray
Pitch - Mating Interface	1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum per Contact	1.5A
Grounding to PCB	Yes

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

78109 Series

Mates With

78103 , 78283 and 78285 Micro SATA Device Plugs

Voltage - Maximum	30V
Material Info	
Reference - Drawing Numbers	
Electrical Model Document	EE-78109-001-001
Packaging Specification	PK-78109-100-001
Product Specification	PS-78109-001-001
S-Parameter Model	SP-78109-001-001
Sales Drawing	SD-78109-001-001

This document was generated on 10/14/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[78109-1001](#)