

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0781192420

Status:

Active

Overview:

Easy-On FFC FPC Connectors

Description:

0.50mm Pitch Easy-On FFC/FPC Connector, Surface Mount, Vertical, Non-ZIF, Standard Footprint, Gold Plating, Black, 24 Circuits

Documents:

- 3D Model (PDF)

Product Specification 781190002-000 (PDF)
- Drawing (PDF)

Packaging Specification 781199200-200 (PDF)
- 3D Model

RoHS Certificate of Compliance (PDF)

General

Product Family

FFC/FPC Connectors

Series

78119

Overview

Easy-On FFC FPC Connectors

Product Name

Easy-On

UPC

889056670708

Physical

Actuator Type

Non-ZIF

Circuits (Loaded)

24

Circuits (maximum)

24

Color - Resin

Black

Contact Position

N/A

Durability (mating cycles max)

10

Mated Height

4.10mm

Material - Metal

Phosphor Bronze

Material - Plating Mating

Gold

Material - Plating Termination

Gold

Material - Resin

Liquid Crystal Polymer

Net Weight

248.970/mg

Number of Rows

1

Orientation

Vertical

PCB Locator

No

PCB Mounting

Surface Mount

PCB Retention

None

Packaging Type

Embossed Tape on Reel

Pitch - Mating Interface

0.50mm

Pitch - Termination Interface

0.50mm

Plating min - Mating

0.100µm

Polarized to PCB

No

Stackable

No

Temperature Range - Operating

-40° to +85°C

Wire/Cable Type

FFC/FPC

Electrical

Current - Maximum per Contact

0.5A

Voltage - Maximum

50V

Material Info

Reference - Drawing Numbers

Packaging Specification


781199200-200

Product Specification

781190002-000

Sales Drawing

781190002-000, 781191002-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

78119 Series

Mates With

Standard FFC/FPC Cables

This document was generated on 09/22/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[78119-2420](#)