

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0797580009

Status:

Active

Overview:

Off-the-Shelf Pre-Crimped Leads

Description:

Pre-Crimped Lead Mini-Fit Female-to-Mini-Fit Female, Tin (Sn) Plating, 300.00mm Length, 18 AWG, Red



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Datasheet \(PDF\)](#)

| General                        |                                 |
|--------------------------------|---------------------------------|
| Product Family                 | Cable Assemblies                |
| Series                         | 79758                           |
| Assembly Configuration         | Pre-crimped Lead Only           |
| Connector to Connector         | Mini-Fit Crimp Terminals        |
| Overview                       | Off-the-Shelf Pre-Crimped Leads |
| Product Name                   | Mini-Fit                        |
| UPC                            | 884982052727                    |
| Physical                       |                                 |
| Cable Length                   | 300.00mm                        |
| Circuits (Loaded)              | 1                               |
| Color - Resin                  | Red                             |
| Gender                         | Female-Female                   |
| Material - Metal               | Brass                           |
| Material - Plating Mating      | Tin                             |
| Material - Plating Termination | Tin                             |
| Net Weight                     | 2.985/g                         |
| Packaging Type                 | Bag                             |
| Single Ended                   | No                              |
| Termination Interface: Style   | Crimp or Compression            |
| Wire Size AWG                  | 18                              |
| Wire/Cable Type                | UL 1061                         |
| Material Info                  |                                 |
| Reference - Drawing Numbers    |                                 |
| Sales Drawing                  | SD-797580001-001                |

|                                                                                                                                                                                     |                                              |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------|
| <b>EU ELV</b><br><b>Not Relevant</b>                                                                                                                                                |                                              |
| <b>EU RoHS</b><br><b>Compliant</b><br><b>REACH SVHC</b><br>Not Contained Per -<br>D(2021)4569-DC (8<br>July 2021)<br><b>Halogen-Free</b><br><b>Status</b><br><b>Not Low-Halogen</b> | <b>China RoHS</b>                            |
| For more information, please visit <a href="#">Contact US</a>                                                                                                                       |                                              |
| China ROHS<br>ELV<br>RoHS Phthalates                                                                                                                                                | Green Image<br>Not Relevant<br>Not Contained |

**Search Parts in this Series**  
[79758](#) Series

**Use With**  
Mini-Fit Receptacle Housings [5557](#) , [42474](#) ,  
[43760](#) , [44516](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[79758-0009](#)