

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0850030309](#)
Status: **Active**
Overview: [DIN 41612](#)
Description: 2.54mm Pitch DIN 41612 Header, Style C, Right-Angle, Through Hole, 0.60µm Selective Gold (Au), Board Lock , 64 Circuits, Lead-Free

Documents:

[3D Model](#) [Packaging Specification PK-85003-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-85003-0001-001 \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family Backplane Connectors
Series [85003](#)
Application Daughtercard
Component Type PCB Header
Overview [DIN 41612](#)
Product Name IEC 603-2/DIN 41612
Style C
UPC 800753873858


Physical

Circuits (Loaded) 64
Circuits (maximum) 96
Durability (mating cycles max) 400
First Mate / Last Break No
Flammability 94V-0
Guide to Mating Part No
Keying to Mating Part Yes
Material - Plating Mating Gold
Net Weight 13.532/g
Number of Columns 16
Number of Pairs Open Pin Field
Number of Rows 3
Orientation Right Angle
PC Tail Length 3.00mm
PCB Locator No
PCB Retention Yes
PCB Thickness - Recommended 1.60mm
Packaging Type Tray
Pitch - Mating Interface 2.54mm
Pitch - Termination Interface 2.54mm
Polarized to PCB Yes
Stackable No
Temperature Range - Operating -55° to +125°C
Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 2.5A
Data Rate 622.0 Mbps
Voltage - Maximum 250V AC (RMS)

Material Info



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[85003](#) Series

Mates With

[85042](#) DIN 41612 Receptacle. [85052](#) DIN 41612 Header

Reference - Drawing Numbers

Packaging Specification	PK-85003-001
Product Specification	PS-85003-0001-001
Sales Drawing	SD-85003-0309

This document was generated on 09/18/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[85003-0309](#)