

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0857321001

Status:

Active

Overview:

Magnetic Jacks

Description:

Gigabit Magnetic Jack, Enabled PSE PoE+ 2x6, with LEDs Left/Green and Right/Green


Documents:	
3D Model	Product Specification PS-85732-001-001 (PDF)
Drawing (PDF)	Packaging Specification PK-85732-001-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Modular Jacks/Plugs
Series	85732
Component Type	PCB Jack
Magnetic	Yes
More Detailed Tech Information	*For product specifications please contact your Molex sales representative
Overview	Magnetic Jacks
Performance Category	5, 5e
Power over Ethernet (PoE)	PoE+
Product Name	Magnetic Jack, RJ45
UPC	884982815131

Physical	
Boot Color	N/A
Color - Resin	Black
Durability (mating cycles max)	750
Inverted / Top Latch	Yes
Jack Height	25.46mm
Lightpipes/LEDs	LEDs
Material - Metal	Brass, Copper Alloy
Material - Plating Mating	Gold
Material - Resin	PBT
Net Weight	76.000/g
Orientation	Right Angle (Side Entry)
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	3.20mm
Packaging Type	Tray
Pitch - Mating Interface	1.27mm, 2.54mm
Pitch - Termination Interface	1.27mm, 2.54mm
Port Configuration	2x6
Positions / Loaded Contacts	8/8
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	0° to +70°C
Termination Interface: Style	Through Hole
Waterproof / Dustproof	No
Wire/Cable Type	N/A

Electrical	
Current - Maximum per Contact	1.0A
Grounding to PCB	Yes
Grounding to Panel	Yes
Shielded	Yes
Voltage - Maximum	57V

Material Info



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Contained Per - ED/108/2014 (17 Dec 2014)	
Halogen-Free Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
85732 Series

Reference - Drawing Numbers

Packaging Specification	PK-85732-001-001
Product Specification	PS-85732-001-001
Sales Drawing	SD-85732-001

This document was generated on 07/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[85732-1001](#)