

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0850030189

Status:

Active

Overview:

DIN 41612

Description:

2.54mm Pitch DIN 41612 Header, Style C, Right-Angle, Through Hole, 0.60µm Selective Gold (Au), 96 Circuits, Lead-Free

Documents:

3D Model

Drawing (PDF)

Product Specification PS-85003-0001-001 (PDF)

Packaging Specification PK-85003-001 (PDF)


RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Backplane Connectors
Series	85003
Application	Daughtercard
Component Type	PCB Header
Overview	DIN 41612
Product Name	IEC 603-2/DIN 41612
Style	C
UPC	800753873810

Physical	
Circuits (Loaded)	96
Circuits (maximum)	96
Durability (mating cycles max)	400
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	Yes
Material - Plating Mating	Gold
Net Weight	14.517/g
Number of Columns	16
Number of Pairs	Open Pin Field
Number of Rows	3
Orientation	Right Angle
PC Tail Length	3.00mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-55° to +125°C
Termination Interface: Style	Through Hole

Electrical	
Current - Maximum per Contact	1.0A
Data Rate	622.0 Mbps
Voltage - Maximum	250V AC (RMS)

Solder Process Data	
Lead-freeProcess Capability	WAVE



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/71/2019 (16 July 2019)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

85003 Series

Mates With

85042 DIN 41612 Receptacle. 85052 DIN 41612 Header

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-85003-001
Product Specification	PS-85003-0001-001
Sales Drawing	SD-85003-0189

This document was generated on 09/18/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[85003-0189](#)