

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936000358

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect Plastic Gable Gland, with Gasket and Nut, M25x1.5 Thread, Grey RAL 7001



Documents:

RoHS Certificate of Compliance (PDF)

|                               |                                       |
|-------------------------------|---------------------------------------|
| General                       |                                       |
| Product Family                | Industrial Connectors / Enclosures    |
| Series                        | 93600                                 |
| Cable Gland Type              | IP68 with Nut and Gasket              |
| IP Rating                     | IP68                                  |
| Overview                      | GWconnect Heavy Duty Connectors (HDC) |
| Product Category              | Cable Glands                          |
| Product Name                  | GWconnect                             |
| Standard                      | DIN EN 50262, EN 60529                |
| UPC                           | 887191852300                          |
| Physical                      |                                       |
| Cable Diameter                | 11.00-18.00mm                         |
| Flammability                  | UL 94V-2                              |
| Gland Color                   | Grey RAL 7001                         |
| Material - Cable Gland        | Polyamide                             |
| Material - Gasket             | NBR                                   |
| Material - Nut                | Polyamide                             |
| Net Weight                    | 22.000/g                              |
| Packaging Type                | Bag                                   |
| Panel Cutout Diameter         | 25.50mm                               |
| Panel Mount                   | Yes                                   |
| Temperature Range - Operating | -40° to +100°C                        |
| Thread Size                   | M25x1.5                               |
| Thread Type                   | (M) Metric                            |
| Waterproof / Dustproof        | Yes                                   |
| Waterproof / Dustproof Type   | IP68                                  |
| Material Info                 |                                       |
| Engineering Number            | 7000.7824.5                           |

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Contained Per - ED/71/2019 (16 July 2019)                 |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Not Reviewed                                                  |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

93600 Series

Use With

Sealed enclosures and boxes

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93600-0358