

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936010166

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect Turned Crimp Contact for 16A Inserts and Modules, Male, Gold (Au)  
Plated Copper Alloy, 0.14-0.37mm² (26-22 AWG), 100 per Bag

Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification

|     |         |
|-----|---------|
| CSA | 256883  |
| UL  | E249674 |

General

|                  |                                       |
|------------------|---------------------------------------|
| Product Family   | Industrial Connectors / Enclosures    |
| Series           | 93601                                 |
| Contact Type     | Turned Crimp                          |
| Overview         | GWconnect Heavy Duty Connectors (HDC) |
| Product Category | Contacts                              |
| Product Name     | GWconnect                             |
| UPC              | 887191874340                          |

Physical

|                    |              |
|--------------------|--------------|
| Gender             | Male         |
| Material - Contact | Copper Alloy |
| Material - Plating | Gold         |
| Net Weight         | 1.400/g      |
| Number of Grooves  | 0            |
| Packaging Type     | Bag          |
| Stripping Length   | 7.50mm       |
| Wire Size AWG      | 22-26        |
| Wire Size mm²      | 0.14-0.37    |

Electrical

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 16.0A |
|-------------------------------|-------|

Material Info

|                    |             |
|--------------------|-------------|
| Engineering Number | 7300.6237.1 |
|--------------------|-------------|



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Contained Per -  
ED/71/2019 (16 July  
2019)  
lead

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

|                 |               |
|-----------------|---------------|
| China ROHS      | Green Image   |
| ELV             | Not Relevant  |
| RoHS Phthalates | Not Contained |

Search Parts in this Series

93601 Series

Mates With

93601 Female Turned Crimp Contact

Use With

S-AC, S-EC, S-EE, S-EEE, S-EHV,S-Q, S-QD, and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-0166