

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** 0936012186  
**Status:** Active  
**Overview:** GWconnect Heavy Duty Connectors (HDC)  
**Description:** GWconnect STD - Standard, Single Lever Hood, Die-cast Aluminum, with 2 Pegs, Top Entry, Size 16A «66x16», Extended Pg16 Threaded Fitting, High Construction, Grey

**Documents:**  
[3D Model](#) [3D Model \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

|                                    |                                                         |
|------------------------------------|---------------------------------------------------------|
| <b>Agency Certification</b>        |                                                         |
| CSA                                | 256883                                                  |
| UL                                 | E249674                                                 |
| <b>General</b>                     |                                                         |
| Product Family                     | Industrial Connectors / Enclosures                      |
| Series                             | 93601                                                   |
| Component Size                     | 16A «66X16»                                             |
| Component Type                     | Single Lever Hood                                       |
| IP Rating                          | IP66                                                    |
| Overview                           | GWconnect Heavy Duty Connectors (HDC)                   |
| Product Category                   | Heavy Duty Connectors                                   |
| Product Name                       | GWconnect                                               |
| Standard                           | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984 |
| Type                               | STD                                                     |
| UPC                                | 887191875910                                            |
| <b>Physical</b>                    |                                                         |
| Entry Location                     | Top                                                     |
| Hood Coating                       | Polyester Powder                                        |
| Hood Color                         | GREY RAL 7037                                           |
| Lock to Mating Part                | Yes                                                     |
| Material - Hood                    | Die-cast Aluminum                                       |
| Material - Peg                     | Stainless Steel                                         |
| Net Weight                         | 204.000/g                                               |
| Number of Pegs                     | 2                                                       |
| Packaging Type                     | Bag                                                     |
| Thread Size                        | Pg16                                                    |
| Thread Type                        | (Pg)                                                    |
| <b>Electrical</b>                  |                                                         |
| Voltage - Maximum                  | 500V                                                    |
| <b>Material Info</b>               |                                                         |
| Engineering Number                 | 7816.4568.0                                             |
| <b>Reference - Drawing Numbers</b> |                                                         |
| Sales Drawing                      | 936012177-000                                           |



Series image - Reference only

|                                                                                                                             |                   |
|-----------------------------------------------------------------------------------------------------------------------------|-------------------|
| <b>EU ELV</b><br>Not Reviewed                                                                                               |                   |
| <b>EU RoHS</b><br>Not Reviewed<br><b>REACH SVHC</b><br>Not Reviewed<br><b>Halogen-Free</b><br><b>Status</b><br>Not Reviewed | <b>China RoHS</b> |
| For more information, please visit <a href="#">Contact US</a>                                                               |                   |
| China ROHS                                                                                                                  | Not Reviewed      |
| ELV                                                                                                                         | Not Reviewed      |
| RoHS Phthalates                                                                                                             | Not Reviewed      |

**Search Parts in this Series**  
93601 Series

**Use With**  
Size 16A «66x16» S-A and S-D Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-2186](#)