

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** 0936012371

**Status:** Active

**Overview:** GWconnect® Heavy Duty Connectors (HDC)

**Description:** GWconnect STD-HV - Standard-High Voltage, Double Lever Hood, Die-cast Aluminum, with 2 Levers, Side Entry, Size 16B «77x27», Pg29 Extended Threaded Fitting, High Construction, Grey

**Documents:**  
RoHS Certificate of Compliance (PDF)

|                             |                                                         |
|-----------------------------|---------------------------------------------------------|
| <b>Agency Certification</b> |                                                         |
| CSA                         | 256883                                                  |
| UL                          | E249674                                                 |
| <b>General</b>              |                                                         |
| Product Family              | Industrial Connectors / Enclosures                      |
| Series                      | 93601                                                   |
| Component Size              | 16B «77X27»                                             |
| Component Type              | Double Lever Hood                                       |
| IP Rating                   | IP66, IP69                                              |
| Overview                    | GWconnect® Heavy Duty Connectors (HDC)                  |
| Product Category            | Heavy Duty Connectors                                   |
| Product Name                | GWconnect                                               |
| Standard                    | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984 |
| Type                        | STD-HV                                                  |
| UPC                         | 887191886763                                            |
| <b>Physical</b>             |                                                         |
| Entry Location              | Side                                                    |
| Hood Coating                | Polyester Powder                                        |
| Hood Color                  | GREY RAL 7037                                           |
| Lock to Mating Part         | Yes                                                     |
| Material - Hood             | Die-cast Aluminum                                       |
| Material - Lever            | Galvanized Steel                                        |
| Number of Levers            | 2                                                       |
| Packaging Type              | Bag                                                     |
| Thread Size                 | Pg29                                                    |
| Thread Type                 | (Pg)                                                    |
| <b>Electrical</b>           |                                                         |
| Voltage - Maximum           | 830V                                                    |
| <b>Material Info</b>        |                                                         |
| Engineering Number          | 7816.5107.2                                             |



Series image - Reference only

|                                                                                                                                                                                     |                   |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|
| <b>EU ELV</b><br>Not Reviewed                                                                                                                                                       |                   |
| <b>EU RoHS</b><br>Not Reviewed                                                                                                                                                      | <b>China RoHS</b> |
| <b>REACH SVHC</b><br>Not Reviewed                                                                                                                                                   |                   |
| <b>Halogen-Free</b><br>Status                                                                                                                                                       |                   |
| <b>Not Reviewed</b><br>Need more information on product environmental compliance?                                                                                                   |                   |
| Email <a href="mailto:productcompliance@molex.com">productcompliance@molex.com</a><br>Please visit the <a href="#">Contact Us</a> section for any non-product compliance questions. |                   |
| China ROHS                                                                                                                                                                          | Not Reviewed      |
| ELV                                                                                                                                                                                 | Not Reviewed      |
| RoHS Phthalates                                                                                                                                                                     | Not Reviewed      |

**Search Parts in this Series**  
93601 Series

**Use With**  
Size 16B «77x27» , S-EHV Inserts with Screw Terminals and S-HSB Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-2371