

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [0936000376](#)  
**Status:** **Active**  
**Overview:**  
**Description:** GWconnect Plastic Gable Gland, with Gasket and Nut, M50x1.5 Thread, Grey RAL 7001

|                  |                                    |
|------------------|------------------------------------|
| <b>General</b>   |                                    |
| Product Family   | Industrial Connectors / Enclosures |
| Series           | <a href="#">93600</a>              |
| Cable Gland Type | IP68 with Nut and Gasket           |
| IP Rating        | IP68                               |
| Overview         | hdc_heavy_duty_connectors          |
| Product Category | Cable Glands                       |
| Product Name     | GWconnect                          |
| Standard         | DIN EN 50262, EN 60529             |
| UPC              | 887191853680                       |

|                               |                |
|-------------------------------|----------------|
| <b>Physical</b>               |                |
| Cable Diameter                | 30.00-38.00mm  |
| Flammability                  | UL 94V-2       |
| Gland Color                   | Grey RAL 7001  |
| Material - Cable Gland        | Polyamide      |
| Material - Gasket             | NBR            |
| Material - Nut                | Polyamide      |
| Net Weight                    | 80.000/g       |
| Packaging Type                | Bag            |
| Panel Cutout Diameter         | 50.50mm        |
| Panel Mount                   | Yes            |
| Temperature Range - Operating | -40° to +100°C |
| Thread Size                   | M50x1.5        |
| Thread Type                   | (M) Metric     |
| Waterproof / Dustproof        | Yes            |
| Waterproof / Dustproof Type   | IP68           |

|                      |             |
|----------------------|-------------|
| <b>Material Info</b> |             |
| Engineering Number   | 7000.7827.5 |

**EU ELV**  
**Not Relevant**

**EU RoHS**  
**Compliant**  
**REACH SVHC**

Not Contained Per -  
ED/71/2019 (16 July  
2019)

**Halogen-Free**  
**Status**

**Not Reviewed**  
For more information, please visit [Contact US](#)

|                 |               |
|-----------------|---------------|
| China ROHS      | Green Image   |
| ELV             | Not Relevant  |
| RoHS Phthalates | Not Contained |

**Search Parts in this Series**  
[93600](#) Series

**Use With**  
Sealed enclosures and boxes

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93600-0376](#)