

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** 0936010728  
**Status:** Active  
**Overview:** GWconnect Heavy Duty Connectors (HDC)  
**Description:** GWconnect HP-HE - High Performance-Harsh Environment, Screw Locking Hood, Zinc Alloy, Side Entry, Size 6B «44x27», M25 Thread, Black

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

|                      |                                                         |
|----------------------|---------------------------------------------------------|
| <b>General</b>       |                                                         |
| Product Family       | Industrial Connectors / Enclosures                      |
| Series               | 93601                                                   |
| Component Size       | 6B «44x27»                                              |
| Component Type       | Screw Locking Hood                                      |
| IP Rating            | IP68, IP69                                              |
| Number of Screws     | 2                                                       |
| Overview             | GWconnect Heavy Duty Connectors (HDC)                   |
| Product Category     | Heavy Duty Connectors                                   |
| Product Name         | GWconnect                                               |
| Standard             | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984 |
| Type                 | HP-HE                                                   |
| UPC                  | 887191845555                                            |
| <b>Physical</b>      |                                                         |
| Entry Location       | Side                                                    |
| Hood Coating         | Epoxy-Polyester Powder                                  |
| Hood Color           | Black RAL 9005                                          |
| Lock to Mating Part  | Yes                                                     |
| Material - Hood      | Zinc Alloy                                              |
| Net Weight           | 445.000/g                                               |
| Packaging Type       | Bag                                                     |
| Thread Size          | M25                                                     |
| Thread Type          | (M) Metric                                              |
| <b>Material Info</b> |                                                         |
| Engineering Number   | 7806.3612.8                                             |



Series image - Reference only

|                                                               |                   |
|---------------------------------------------------------------|-------------------|
| <b>EU ELV</b><br>Not Reviewed                                 |                   |
| <b>EU RoHS</b><br>Not Reviewed                                | <b>China RoHS</b> |
| <b>REACH SVHC</b><br>Not Reviewed                             |                   |
| <b>Halogen-Free</b><br>Status                                 |                   |
| <b>Not Reviewed</b>                                           |                   |
| For more information, please visit <a href="#">Contact US</a> |                   |
| China ROHS                                                    | Not Reviewed      |
| ELV                                                           | Not Reviewed      |
| RoHS Phthalates                                               | Not Reviewed      |

**Search Parts in this Series**  
93601 Series

**Use With**  
Size 6B «44x27» S-D, S-DD, S-E, S-EP, S-EE, S-EEE, S-HSB, S-K, and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-0728