

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** 0936011670  
**Status:** Active  
**Overview:** GWconnect Heavy Duty Connectors (HDC)  
**Description:** GWconnect STD - Standard, Single Lever Hood, Die-cast Aluminum, with 2 Pegs, Side Entry, Size 10B «57x27», Pg21 Thread, High Construction, Grey



|                               |                                                         |
|-------------------------------|---------------------------------------------------------|
| <b>Documents:</b>             |                                                         |
| <a href="#">Drawing (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>    |
| <b>Agency Certification</b>   |                                                         |
| CSA                           | 256883                                                  |
| UL                            | E249674                                                 |
| <b>General</b>                |                                                         |
| Product Family                | Industrial Connectors / Enclosures                      |
| Series                        | 93601                                                   |
| Component Size                | 10B «57X27»                                             |
| Component Type                | Single Lever Hood                                       |
| IP Rating                     | IP66                                                    |
| Overview                      | <a href="#">GWconnect Heavy Duty Connectors (HDC)</a>   |
| Product Category              | Heavy Duty Connectors                                   |
| Product Name                  | GWconnect                                               |
| Standard                      | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984 |
| Type                          | STD                                                     |
| UPC                           | 887191840758                                            |
| <b>Physical</b>               |                                                         |
| Entry Location                | Side                                                    |
| Hood Coating                  | Polyester Powder                                        |
| Hood Color                    | GREY RAL 7037                                           |
| Lock to Mating Part           | Yes                                                     |
| Material - Hood               | Die-cast Aluminum                                       |
| Material - Peg                | Stainless Steel                                         |
| Net Weight                    | 192.000/g                                               |
| Number of Pegs                | 2                                                       |
| Packaging Type                | Bag                                                     |
| Thread Size                   | Pg21                                                    |
| Thread Type                   | (Pg)                                                    |
| <b>Electrical</b>             |                                                         |
| Voltage - Maximum             | 500V                                                    |
| <b>Material Info</b>          |                                                         |
| Engineering Number            | 7810.6479.5                                             |

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

**China RoHS**

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

93601 Series

**Use With**

Size 10B «57x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-1670