

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936013795

Status:

Active

Overview:

Description:

GWconnect STD-HV - Standard-High Voltage, Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Double Top Entry, Size 24B «104x27», M32x2 Extended Threaded Fitting, Grey, High Construction

|                      |                                                         |
|----------------------|---------------------------------------------------------|
| Agency Certification |                                                         |
| CSA                  | 256883                                                  |
| UL                   | E249674                                                 |
| General              |                                                         |
| Product Family       | Industrial Connectors / Enclosures                      |
| Series               | 93601                                                   |
| Component Size       | 24B «104X27»                                            |
| Component Type       | Double Lever Hood                                       |
| IP Rating            | IP66                                                    |
| Overview             | hdc_heavy_duty_connectors                               |
| Product Category     | Heavy Duty Connectors                                   |
| Product Name         | GWconnect                                               |
| Standard             | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984 |
| Type                 | STD-HV                                                  |
| UPC                  | 887191861906                                            |
| Physical             |                                                         |
| Entry Location       | Top                                                     |
| Hood Coating         | Polyester Powder                                        |
| Hood Color           | GREY RAL 7037                                           |
| Lock to Mating Part  | Yes                                                     |
| Material - Hood      | Die-cast Aluminum                                       |
| Material - Peg       | Stainless Steel                                         |
| Net Weight           | 412.000/g                                               |
| Number of Pegs       | 4                                                       |
| Packaging Type       | Bag                                                     |
| Thread Size          | M32x2                                                   |
| Thread Type          | (M) Metric                                              |
| Electrical           |                                                         |
| Voltage - Maximum    | 830V                                                    |
| Material Info        |                                                         |
| Engineering Number   | 7824.6625.2                                             |

|                                                               |              |
|---------------------------------------------------------------|--------------|
| EU ELV                                                        |              |
| Not Reviewed                                                  |              |
| EU RoHS                                                       | China RoHS   |
| Not Reviewed                                                  |              |
| REACH SVHC                                                    |              |
| Not Reviewed                                                  |              |
| Halogen-Free                                                  |              |
| Status                                                        |              |
| Not Reviewed                                                  |              |
| For more information, please visit <a href="#">Contact US</a> |              |
| China ROHS                                                    | Not Reviewed |
| ELV                                                           | Not Reviewed |
| RoHS Phthalates                                               | Not Reviewed |

Search Parts in this Series

93601 Series

Use With

Size 24B «104x27» , S-EHV Inserts with Screw Terminals and S-HSB Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-3795](#)