

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [0936013981](#)  
**Status:** **Active**  
**Overview:** GWconnect Heavy Duty Connectors (HDC)  
**Description:** GWconnect STD - Standard, Single Lever Surface Mount Housing, Die-cast Aluminum, with 1 Lever, with Cover, with Gasket, Size 24B «104x27», Pg29 Thread, High Construction, Grey



|                                    |                                                         |
|------------------------------------|---------------------------------------------------------|
| <b>Documents:</b>                  |                                                         |
| <a href="#">Drawing (PDF)</a>      | <a href="#">RoHS Certificate of Compliance (PDF)</a>    |
| <b>Agency Certification</b>        |                                                         |
| CSA                                | 256883                                                  |
| UL                                 | E249674                                                 |
| <b>General</b>                     |                                                         |
| Product Family                     | Industrial Connectors / Enclosures                      |
| Series                             | <a href="#">93601</a>                                   |
| Component Size                     | 24B «104X27»                                            |
| Component Type                     | Single Lever SMT Housing                                |
| IP Rating                          | IP66                                                    |
| Overview                           | <a href="#">GWconnect Heavy Duty Connectors (HDC)</a>   |
| Product Category                   | Heavy Duty Connectors                                   |
| Product Name                       | GWconnect                                               |
| Standard                           | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984 |
| Type                               | STD                                                     |
| UPC                                | 887191873992                                            |
| <b>Physical</b>                    |                                                         |
| Cover Coating                      | Polyester Powder                                        |
| Cover Color                        | Grey RAL 7037                                           |
| Housing Coating                    | Polyester Powder                                        |
| Housing Color                      | Grey RAL 7037                                           |
| Lock to Mating Part                | Yes                                                     |
| Material - Cover                   | Die-cast Aluminum                                       |
| Material - Gasket                  | NBR                                                     |
| Material - Housing                 | Die-cast Aluminum                                       |
| Material - Lever                   | Galvanized Steel                                        |
| Mounting Style                     | Surface Mount                                           |
| Net Weight                         | 515.000/g                                               |
| Number of Levers                   | 1                                                       |
| Packaging Type                     | Bag                                                     |
| Thread Size                        | Pg29                                                    |
| Thread Type                        | (Pg)                                                    |
| <b>Electrical</b>                  |                                                         |
| Voltage - Maximum                  | 500V                                                    |
| <b>Material Info</b>               |                                                         |
| Engineering Number                 | 7824.7298.0                                             |
| <b>Reference - Drawing Numbers</b> |                                                         |
| Sales Drawing                      | 936013976-000                                           |

|                                                                                                                                        |                                              |
|----------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------|
| <b>EU ELV</b><br><b>Not Relevant</b>                                                                                                   |                                              |
| <b>EU RoHS</b><br><b>Compliant</b><br><b>REACH SVHC</b><br>Not Reviewed<br><b>Halogen-Free</b><br><b>Status</b><br><b>Not Reviewed</b> | <b>China RoHS</b>                            |
| For more information, please visit <a href="#">Contact US</a>                                                                          |                                              |
| China ROHS<br>ELV<br>RoHS Phthalates                                                                                                   | Green Image<br>Not Relevant<br>Not Contained |

**Search Parts in this Series**  
[93601](#) Series

**Use With**  
Size 24B «104x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-3981](#)