

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

|                      |                                                                                                                                                |
|----------------------|------------------------------------------------------------------------------------------------------------------------------------------------|
| Part Number:         | 0936014437                                                                                                                                     |
| Status:              | Active                                                                                                                                         |
| Overview:            | GWconnect Heavy Duty Connectors (HDC)                                                                                                          |
| Description:         | GWconnect STD - Standard, Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Side Entry, Size 32B «77x62», M50 Thread, High Construction, Grey |
| Documents:           |                                                                                                                                                |
| Drawing (PDF)        | RoHS Certificate of Compliance (PDF)                                                                                                           |
| Agency Certification |                                                                                                                                                |
| CSA                  | 256883                                                                                                                                         |
| UL                   | E249674                                                                                                                                        |
| General              |                                                                                                                                                |
| Product Family       | Industrial Connectors / Enclosures                                                                                                             |
| Series               | 93601                                                                                                                                          |
| Component Size       | 32B «77X62»                                                                                                                                    |
| Component Type       | Double Lever Hood                                                                                                                              |
| IP Rating            | IP66                                                                                                                                           |
| Overview             | GWconnect Heavy Duty Connectors (HDC)                                                                                                          |
| Product Category     | Heavy Duty Connectors                                                                                                                          |
| Product Name         | GWconnect                                                                                                                                      |
| Standard             | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984                                                                                        |
| Type                 | STD                                                                                                                                            |
| UPC                  | 887191895338                                                                                                                                   |
| Physical             |                                                                                                                                                |
| Entry Location       | Side                                                                                                                                           |
| Hood Coating         | Polyester Powder                                                                                                                               |
| Hood Color           | GREY RAL 7037                                                                                                                                  |
| Lock to Mating Part  | Yes                                                                                                                                            |
| Material - Hood      | Die-cast Aluminum                                                                                                                              |
| Material - Peg       | Stainless Steel                                                                                                                                |
| Net Weight           | 396.000/g                                                                                                                                      |
| Number of Pegs       | 4                                                                                                                                              |
| Packaging Type       | Bag                                                                                                                                            |
| Thread Size          | M50                                                                                                                                            |
| Thread Type          | (M) Metric                                                                                                                                     |
| Electrical           |                                                                                                                                                |
| Voltage - Maximum    | 500V                                                                                                                                           |
| Material Info        |                                                                                                                                                |
| Engineering Number   | 7832.6577.5                                                                                                                                    |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

93601 Series

Use With

Size 32B «77x62» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts and Housings

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-4437