

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0986581223

Status:


Active

Overview:

MOX Products

Description:

MOX Crimp Terminal, Female, 0.635mm, 20-24 AWG (0.22-0.50mm²), Reel, Selective Gold



Series image - Reference only

Documents:	
3D Model	Application Specification AS-98658-001-CH-001 (PDF)
Drawing (PDF)	Packaging Specification PK-98658-006-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-98658-001-001 (PDF)	

General	
Product Family	Crimp Terminals
Series	98658
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Terminal has Stainless Steel Sleeve
Crimp Quality Equipment	Yes
Overview	MOX Products
Product Name	MOX
UPC	756054551417
Physical	
Durability (mating cycles max)	20
Gender	Female
Material - Metal	Copper-Nickel-Silicon, Stainless Steel
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.120/g
Packaging Type	Reel
Plating min - Mating	0.406µm
Plating min - Termination	1.016µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.20-1.50mm
Wire Size AWG	20, 22
Wire Size mm²	0.32-0.51
Electrical	
Current - Maximum per Contact	7.5A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-98658-001-001, AS-98658-001-CH-001
Crimp Specification	CS-98658-001-001
Packaging Specification	PK-98658-006-001
Sales Drawing	SD-98658-004-001

EU ELV
Compliant

EU RoHS
Compliant

REACH SVHC
Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free
Status
Low-Halogen

For more information, please visit [Contact US](#)

China ROHS
ELV
RoHS Phthalates

Green Image
Compliant
Not Contained

Search Parts in this Series

98658 Series

Use With

all 0.635mm MOX Housings

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool	638119300
MOX Extraction Tool	638132600
Extractor Tool for 2.80mm Crimp Terminals	638136900
Extractor Tool for 2.80mm Crimp Terminals	638137000
Extractor Tool for MOX 0.635mm	638138400

Receptacle Crimp
Terminals
Extractor Tool for 638138500
MOX 0.635mm
Receptacle Crimp
Terminals
Extractor Tool for 638244400
MOX 0.635mm
Receptacle Crimp
Terminals
FineAdjust Applicator638666100

This document was generated on 12/14/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[98658-1223](#)