

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

**Part Number:** [0987811004](#)  
**Status:** **Active**  
**Description:** NSCC Pin Connector, 3.33mm Pitch, 1.50mm, Shorting Bar, Long, 5 Circuit, Blue

**Documents:**

|                                                                     |                                                                |
|---------------------------------------------------------------------|----------------------------------------------------------------|
| <a href="#">Drawing (PDF)</a>                                       | <a href="#">Packaging Specification PK-98781-001-001 (PDF)</a> |
| <a href="#">Application Specification AS-98781-005-001 (PDF)</a>    | <a href="#">RoHS Certificate of Compliance (PDF)</a>           |
| <a href="#">Application Specification AS-98781-005-CH-001 (PDF)</a> |                                                                |

**Application tooling part link**

|                               |            |
|-------------------------------|------------|
| Application Tooling Part Link | 63813-4100 |
| Application Tooling Part Link | 63813-4200 |

**General**

|                |                       |
|----------------|-----------------------|
| Product Family | Crimp Housings        |
| Series         | <a href="#">98781</a> |
| Application    | Wire-to-Wire          |
| Product Name   | SICMA                 |
| UPC            | 822350871402          |

**Physical**

|                               |               |
|-------------------------------|---------------|
| Circuits (maximum)            | 5             |
| Circuits Detail               | 5             |
| Color - Resin                 | Blue          |
| Gender                        | Plug          |
| Glow-Wire Capable             | No            |
| Lock to Mating Part           | Yes           |
| Material - Resin              | PBT           |
| Net Weight                    | 9.500/g       |
| Number of Rows                | 1             |
| Packaging Type                | Carton        |
| Panel Mount                   | No            |
| Pitch - Mating Interface      | 3.33mm        |
| Polarized to Mating Part      | Yes           |
| Stackable                     | No            |
| Temperature Range - Operating | -40° to +85°C |

**Solder Process Data**

|                             |     |
|-----------------------------|-----|
| Lead-freeProcess Capability | N/A |
|-----------------------------|-----|

**Material Info**

**Reference - Drawing Numbers**

|                           |                                       |
|---------------------------|---------------------------------------|
| Application Specification | AS-98781-005-001, AS-98781-005-CH-001 |
| Packaging Specification   | PK-98781-001-001                      |
| Sales Drawing             | SD-98781-001-001                      |



Series image - Reference only

**EU ELV**  
**Compliant**

**EU RoHS**  
**Compliant**  
**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**  
**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

|                 |               |
|-----------------|---------------|
| China ROHS      | Not Relevant  |
| ELV             | Compliant     |
| RoHS Phthalates | Not Contained |

**Search Parts in this Series**  
[98781](#) Series

**Mates With**  
[987841004](#) NSCC 3.33mm Pitch Female Housing

**Use With**  
1.50mm Size FCI SICMA Male Terminal

**Application Tooling | FAQ**  
*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

| Description                           | Product #                 |
|---------------------------------------|---------------------------|
| Extractor Tool for 5-Way Male Housing | <a href="#">638134100</a> |
| Extractor Tool for 5-Way Male Housing | <a href="#">638134200</a> |

This document was generated on 12/28/2020

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[98781-1004](#)