

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936030094

Status:


Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect Connector Kit, 24 Pole, Series S-E Female-Male Inserts, M25 Metal Cable Gland, M25 Die-cast Aluminum Hood-Side Entry, Surface Mount Housing-Vertical, 2 Lever, Size 24B «104x27», Grey



Documents:

RoHS Certificate of Compliance (PDF)

|                                                                                                                         |                                       |
|-------------------------------------------------------------------------------------------------------------------------|---------------------------------------|
| Kit components                                                                                                          |                                       |
| Kit Components                                                                                                          |                                       |
| 936000047 M25 Gland, 936013770 M25 Hood, 936010307 Male Insert, 936010297 Female Insert, 936013522 SMT Vertical Housing |                                       |
|                                                                                                                         |                                       |
| General                                                                                                                 |                                       |
| Product Family                                                                                                          | Industrial Connectors / Enclosures    |
| Series                                                                                                                  | 93603                                 |
| Component Size                                                                                                          | 24B «104X27»                          |
| Component Type                                                                                                          | Connector Kit - Female+Male           |
| Insert Series                                                                                                           | S-E                                   |
| Overview                                                                                                                | GWconnect Heavy Duty Connectors (HDC) |
| Product Category                                                                                                        | Heavy Duty Connectors                 |
| Product Name                                                                                                            | GWconnect                             |
| UPC                                                                                                                     | 887191865744                          |
|                                                                                                                         |                                       |
| Physical                                                                                                                |                                       |
| Lock to Mating Part                                                                                                     | Yes                                   |
| Mounting Style                                                                                                          | Surface Mount                         |
| Net Weight                                                                                                              | 820.500/g                             |
| Packaging Type                                                                                                          | Bag                                   |
| Thread Size                                                                                                             | M25                                   |
| Thread Type                                                                                                             | (M) Metric                            |
|                                                                                                                         |                                       |
| Electrical                                                                                                              |                                       |
| Current - Maximum per Contact                                                                                           | 16.0A                                 |
| Voltage - Maximum                                                                                                       | 500V                                  |
|                                                                                                                         |                                       |
| Material Info                                                                                                           |                                       |
| Engineering Number                                                                                                      | 7924.7762.5                           |

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
|                                                               |               |
| EU RoHS                                                       | China RoHS    |
| Compliant with Exemption 6(c)                                 |               |
| REACH SVHC                                                    |               |
| Contained Per - ED/71/2019 (16 July 2019)                     |               |
| lead                                                          |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Not Reviewed                                                  |               |
| For more information, please visit <a href="#">Contact US</a> |               |
|                                                               |               |
| China ROHS                                                    | 50 Image      |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

93603 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93603-0094](#)