

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1060243600

Status:

Active

Overview:

Optical Connectivity Solutions

Description:

LC Connector, Multimode, 128µm Ceramic Ferrule, 2.00mm Simplex Cable, Beige Housing, 90°



Series image - Reference only

Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Datasheet \(PDF\)](#)

|                               |                                |
|-------------------------------|--------------------------------|
| General                       |                                |
| Product Family                | Fiber Optic Connectors         |
| Series                        | 106024                         |
| Cable Size                    | 2.00mm                         |
| Material - Housing            | PEI                            |
| Mode                          | Multimode                      |
| Overview                      | Optical Connectivity Solutions |
| Product Name                  | LC                             |
| UPC                           | 822350259248                   |
| Wire/Cable Type               | Simplex                        |
| Physical                      |                                |
| Alignment Sleeve              | N/A                            |
| Angled Physical Contact (APC) | No                             |
| Boot Color                    | Beige                          |
| Boot Type                     | 90°                            |
| Color - Resin                 | Beige                          |
| Ferrule Hole Size             | 128µm                          |
| Ferrule Material              | Ceramic                        |
| Gender                        | Plug                           |
| Mounting Style                | Adhesive                       |
| Net Weight                    | 1.905/g                        |
| Ports                         | 1                              |
| Solder Process Data           |                                |
| Lead-freeProcess Capability   | N/A                            |
| Material Info                 |                                |
| Engineering Number            | 860243600                      |
| Reference - Drawing Numbers   |                                |
| Sales Drawing                 | SD-1060BB-BBBB-001             |

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Contained Per - D(2020)9139-DC (19 Jan 2021)              |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Not Low-Halogen                                               |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

106024 Series

Mates With

106115 LC Duplex EMI Adapter, 106123 LC Quad Adapter, 106124 LC Simplex Adapter, 106125 LC Duplex Adapter, 106126 LC Duplex Adapter, 106127 LC Duplex Adapter, 106128 LC Duplex Adapter

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

106024-3600