

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0988211035](#)
Status: **Active**
Overview: NSCC - New Standard Casing Contact
Description: NSCC, Receptacle Connector Hybrid, Single Part, Unsealed 3 Circuits, Green

Documents:
[3D Model](#) [Application Specification 988210001-PS-CH-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [Application Specification AS-98821-001-001 \(PDF\)](#)
[Product Specification PS-98821-001-001 \(PDF\)](#) [Packaging Specification PK-31301-635-001 \(PDF\)](#)
[Application Specification 988210001-AS-CH-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Application tooling part link
Application Tooling Part Link 63813-3800

General
Product Family Crimp Housings
Series [98821](#)
Application Power, Wire-to-Wire
Overview NSCC - New Standard Casing Contact
Product Name NSCC
UPC 883906171278

Physical
Circuits (maximum) 3
Color - Resin Green
Gender Receptacle
Glow-Wire Capable No
Keying to Mating Part Yes
Lock to Mating Part Yes
Material - Resin Polyester
Net Weight 2.430/g
Number of Rows 1
Packaging Type Carton
Panel Mount No
Pitch - Mating Interface 4.20mm, 5.00mm
Polarized to Mating Part Yes
Ports 1
Stackable No
Temperature Range - Operating -40° to +85°C

Solder Process Data
Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers
Application Specification 988210001-AS-CH-001, 988210001-PS-CH-001, AS-98821-001-001
Packaging Specification PK-31301-635-001
Product Specification PS-98821-001-001
Sales Drawing SD-98820-001-001, SD-98821-001-001



Series image - Reference only

EU ELV
Compliant

EU RoHS
Compliant
REACH SVHC

China RoHS

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free
Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[98821](#) Series

Mates With
Counterpart per Interface Drawing, Contact Molex

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	Product #
Description	
Extractor Tool for Unsealed Receptacle Connectors	638133800

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[98821-1035](#)