

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1041148017

Status:


Active

Overview:

Easy-On FFC FPC Connectors

Description:

0.50mm Pitch Easy-On FFC/FPC Slim Connector, Surface Mount, Right-Angle,ZIF, Bottom Contact Style, Front Flip, 1.50mm Mated Height, Gold (Au) Plating, 80 Circuits



Series image - Reference only

Documents:	
3D Model (PDF)	Product Specification 1041148017-000 (PDF)
3D Model	Packaging Specification PK-104114-001-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	FFC/FPC Connectors
Series	104114
Comments	Black Actuator
Overview	Easy-On FFC FPC Connectors
Product Name	Easy-On
UPC	884982410640
Physical	
Actuator Type	Front Flip
Circuits (Loaded)	80
Circuits (maximum)	80
Color - Resin	Natural
Contact Position	Bottom
Durability (mating cycles max)	20
Mated Height	1.50mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	0.459/g
Number of Rows	1
Orientation	Right Angle
PCB Mounting	Surface Mount
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.102µm
Plating min - Termination	0.051µm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-20° to +85°C
Wire/Cable Type	FFC/FPC
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	50V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	250
Material Info	

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

104114 Series

Reference - Drawing Numbers

Packaging Specification	PK-104114-001-001
Product Specification	1041148017-000
Sales Drawing	SD-104114-001

This document was generated on 04/05/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[104114-8017](#)