

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1053860003

Status:


Active

Overview:

Spring Clips for Mobile Devices

Description:

Reinforced, Anti-Snag Spring Clip, 1.00mm Width, 0.25µm Gold (Au) Plating, 0.40mm - 0.80mm Working Range (Height)



Documents:

Drawing (PDF)

Product Specification PS-105386-001-001 (PDF)

Packaging Specification PK-105386-001-001 (PDF)

Test Summary TS-105386-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

|                                |                                 |
|--------------------------------|---------------------------------|
| General                        |                                 |
| Product Family                 | Accessories                     |
| Series                         | 105386                          |
| Component Type                 | Clip                            |
| Overview                       | Spring Clips for Mobile Devices |
| Product Name                   | Spring Clip                     |
| UPC                            | 889056228824                    |
| Physical                       |                                 |
| Circuits (Loaded)              | 1                               |
| Circuits (maximum)             | 1                               |
| Material - Metal               | Stainless Steel                 |
| Material - Plating Mating      | Gold                            |
| Material - Plating Termination | Gold                            |
| Net Weight                     | 0.033/g                         |
| Packaging Type                 | Embossed Tape on Reel           |
| Plating min - Mating           | 0.254µm                         |
| Temperature Range - Operating  | -40° to +85°C                   |
| Termination Interface: Style   | Solder                          |
| Electrical                     |                                 |
| Current - Maximum per Contact  | 1.5A                            |
| Material Info                  |                                 |
| Reference - Drawing Numbers    |                                 |
| Packaging Specification        | PK-105386-001-001               |
| Product Specification          | PS-105386-001-001               |
| Sales Drawing                  | SD-105386-002-001               |
| Test Summary                   | TS-105386-001-001               |

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Contained Per - D(2021)4569-DC (8 July 2021)              |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Low-Halogen                                                   |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

105386 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

105386-0003