

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1060051000](#)  
**Status:** **Active**  
**Overview:** [Optical Connectivity Solutions](#)  
**Description:** MPO Loopback, Singlemode, 12 Fiber, 9/125µm, Standard Pin Out

**Documents:**  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

|                        |                                                |
|------------------------|------------------------------------------------|
| <b>General</b>         |                                                |
| Product Family         | Fiber Optic Assemblies                         |
| Series                 | <a href="#">106005</a>                         |
| Boot Type              | N/A                                            |
| Connector to Connector | N/A                                            |
| Mode                   | Singlemode                                     |
| Overview               | <a href="#">Optical Connectivity Solutions</a> |
| Product Name           | MPO                                            |
| UPC                    | 800756925332                                   |
| <b>Physical</b>        |                                                |
| Cable Length           | LOOPBACK                                       |
| Cable Size             | 9/125µm                                        |
| Fiber (Core/Cladding)  | 9/125µm                                        |
| Net Weight             | 96.180/g                                       |
| Single Ended           | Yes                                            |
| Wire/Cable Type        | Ribbon Cable                                   |

**Material Info**

**Reference - Drawing Numbers**  
Sales Drawing SD-106005-1000-001



|                                                                                                                                                                                                                                                      |                                              |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------|
| <b>EU ELV</b><br><b>Not Relevant</b>                                                                                                                                                                                                                 |                                              |
| <b>EU RoHS</b><br><b>Compliant</b><br><b>REACH SVHC</b><br>Not Contained Per -<br>D(2020)9139-DC (19<br>Jan 2021)<br><b>Halogen-Free</b><br><b>Status</b><br><b>Not Low-Halogen</b><br>For more information, please visit <a href="#">Contact US</a> | <b>China RoHS</b>                            |
| China ROHS<br>ELV<br>RoHS Phthalates                                                                                                                                                                                                                 | Green Image<br>Not Relevant<br>Not Contained |

**Search Parts in this Series**  
[106005](#) Series

**Mates With**  
MTP Adapter [106181](#) , [106114](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[106005-1000](#)