

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1300230004](#)  
**Status:** **Active**  
**Overview:** [Push-Button Pendant Products](#)  
**Description:** Super-Safeway Single Button, 3 Pin, Single-Pole, Single-Throw, Normally Open, 10A, Snap Action Switch, NBR/PVC Switch Boot, 125/250V AC, Mini-Change Connection

**Documents:**

|                                                                       |                                                      |
|-----------------------------------------------------------------------|------------------------------------------------------|
| <a href="#">Drawing (PDF)</a>                                         | <a href="#">Datasheet (PDF)</a>                      |
| <a href="#">Application Specification 1300230001APPSPEC-000 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a> |

**Agency Certification**

|    |        |
|----|--------|
| UL | E70531 |
|----|--------|

**General**

|                  |                                              |
|------------------|----------------------------------------------|
| Product Family   | Push Buttons / Testers                       |
| Series           | <a href="#">130023</a>                       |
| Enclosure Rating | Weather Resistant                            |
| Overview         | <a href="#">Push-Button Pendant Products</a> |
| Product Name     | Super-Safeway                                |
| Type             | Enabling Switch, PushButton Pendant Station  |
| UPC              | 78678855509                                  |

**Physical**

|                     |          |
|---------------------|----------|
| Cord Diameter       | N/A      |
| Cord Grip Body Size | N/A      |
| Cord Length         | N/A      |
| Emergency Stop      | No       |
| Material - Body     | Nylon    |
| Net Weight          | 70.760/g |
| Number of Speeds    | Single   |
| Packaging Type      | Carton   |
| Poles               | 1        |

**Electrical**

|                   |                   |
|-------------------|-------------------|
| Cord Type         | N/A               |
| Voltage - Maximum | 125V AC / 250V AC |

**Material Info**

|                    |       |
|--------------------|-------|
| Engineering Number | 55504 |
|--------------------|-------|

**Reference - Drawing Numbers**

|                           |                        |
|---------------------------|------------------------|
| Application Specification | 1300230001_APPSPEC-000 |
| Sales Drawing             | SD-130023-005-001      |



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

|                 |              |
|-----------------|--------------|
| China ROHS      | Not Reviewed |
| ELV             | Not Relevant |
| RoHS Phthalates | Not Reviewed |

**Search Parts in this Series**

[130023](#) Series

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300230004 55504