

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1203410308

Status:

Active

Overview:

Brad Industrial Ethernet Solutions

Description:

Micro-Change (M12) CAT6A Double-Ended Cordset, 8 Poles, Male (Straight) to Male (Straight), 26 AWG, Blue Shielded PUR Cable, 20.0m (65.62') Length



Documents:

Drawing (PDF)

Product Specification PS-120341-001-001 (PDF)

Packaging Specification PK-120341-300-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Cordsets
Series	120341
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
IP Rating	IP67
Material - Contact	Brass
Overview	Brad Industrial Ethernet Solutions
Performance Category	6A
Product Name	Micro-Change (M12) Cat6A
Protocol	N/A
Region	America, Asia, Europe
Type	Double Ended
UPC	889056017701
Physical	
Cable Diameter	6.40mm (.252")
Cable Length	20.0m (65.62")
Color - Cable Jacket	Blue
Coupling Style	Threaded
Gender	Male-Male
Keyway	X-coded
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	926.000/g
Orientation	Straight to Straight
Poles	8
Temperature Range - Operating	-40° to +70°C
Wire Size AWG	26
Wire/Cable Type	Shielded PUR
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	50V AC / 60 DC
Material Info	
Engineering Number	E22E06020M200
Reference - Drawing Numbers	
Packaging Specification	PK-120341-300-001
Product Specification	PS-120341-001-001
Sales Drawing	1203410300-000

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2020)9139-DC (19 Jan 2021)

Lead

Halogen-Free Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

120341 Series

Mates With

120341 Micro-Change CAT6A Receptacles

This document was generated on 01/07/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1203410308