

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1203410510

Status:

Active

Overview:

Brad Industrial Ethernet Solutions

Description:

Micro-Change M12 to Standard RJ-45 CAT6A Double-Ended Cordset, 8 Poles, Male (Straight) to Male (Straight), 26 AWG, Shielded PUR Cable, 40.0m (131.20') Length

Documents:

Drawing (PDF)

Product Specification PS-120341-140-001 (PDF)

Packaging Specification PK-120341-140-001 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Connector End A

Connector End B

IP Rating

Material - Contact

Overview

Performance Category

Product Name

Protocol

Region

Type

UPC

Industrial Cordsets

120341

Micro-Change (M12)

RJ-45 (standard)

IP20, IP67

Brass

Brad Industrial Ethernet Solutions

6A

Micro-Change (M12) Cat6A, RJ45

N/A

America, Asia, Europe

Double Ended

889056017626

Physical

Cable Diameter

Cable Length

Color - Cable Jacket

Coupling Style

Gender

Keyway

LED Indicator

Material - Cable Jacket

Material - Connector Body

Material - Coupling Nut

Material - Plating Mating

Orientation

Poles

Temperature Range - Operating

Wire Size AWG

Wire/Cable Type

6.40mm (.252")

40.0m (131.20")

Blue

Threaded

Male-Male

X-coded

No

PUR

PUR

Nickel-plated Brass

Gold

Straight to Straight

8

-40°C to +70°C

26

Shielded PUR

Electrical

Current - Maximum per Contact

Voltage - Maximum

0.5A

48V

Material Info

Engineering Number

E26E06020M400

Reference - Drawing Numbers

Packaging Specification


Product Specification

Sales Drawing

PK-120341-140-001

PS-120341-140-001

1203410500-000, 1203410510-000



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China RoHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

120341 Series

Mates With

120341 Micro-Change CAT6A Receptacles

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

120341-0510