

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300830262

Status:

Active

Overview:

Reels - Woodhead

Description:

Woodhead POW-R-MITE Industrial Duty Cable Reel, 14/4 SOW, 7.62m (25.0') Cord Length

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA	LR29921	
UL	E22769	
General		
Product Family	Electric Reels	
Series	130083	
Cable Length	N/A	
Comments	Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.	
Depth	0.34m (13.50")	
Duty	Industrial	
Enclosure Rating	NEMA 4	
Height	0.37m (14.50")	
NEMA Configuration	N/A	
Overview	Reels - Woodhead	
Product Name	POW-R-MITE	
Type	Cable Reel	
UPC	78678879363	
Width	244.35mm (9.620")	
Physical		
Cable Movement	Ratchet Lock	
Cord Length	7.62m (25.0')	
Drum Lock	Ratchet	
Guide Arm	5° increments over 270° Arc	
Material - Coating	Powder Coating	
Material - Housing	Cast Aluminum	
Mounting Style	Rigid	
Net Weight	19504.456/g	
Number of Conductors	4	
Packaging Type	Carton	
Primary Cord/Cable Entry	1" NPT	
Retraction Weight	1.8kg (4.0 lb)	
Wire Size AWG	14	
Electrical		
Bulb Included	N/A	
Cord Type	14/4 SOW	
Current - Maximum per Contact	11.0A	
GFCI	No	
Lamp Type	N/A	
Lamp Wattage - Maximum	N/A	
On/Off Switch	N/A	
Voltage - Maximum	600V	
Material Info		
Engineering Number	9363	



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130083 Series

This document was generated on 07/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1300830262](#)