

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300840138

Status:

Active

Overview:

Reels - Woodhead

Description:

Woodhead POW-R-MITE Heavy Duty Cable Reel with Retraction Weight of 4lbs., 16/4 SOW, 21.34m (70.0') Cord Length with Flying Leads

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

|                               |                                                                                  |
|-------------------------------|----------------------------------------------------------------------------------|
| Agency Certification          |                                                                                  |
| CSA                           | LR29921                                                                          |
| General                       |                                                                                  |
| Product Family                | Electric Reels                                                                   |
| Series                        | 130084                                                                           |
| Cable Length                  | N/A                                                                              |
| Comments                      | Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag. |
| Depth                         | 0.48m (19.00")                                                                   |
| Duty                          | Heavy                                                                            |
| Enclosure Rating              | NEMA 3                                                                           |
| Height                        | 0.52m (20.50")                                                                   |
| NEMA Configuration            | N/A                                                                              |
| Overview                      | Reels - Woodhead                                                                 |
| Product Name                  | POW-R-MITE                                                                       |
| Type                          | Cable Reel                                                                       |
| UPC                           | 78678827480                                                                      |
| Width                         | 423.42mm (16.670")                                                               |
| Physical                      |                                                                                  |
| Cable Movement                | Ratchet Lock                                                                     |
| Cord Length                   | 21.34m (70.0')                                                                   |
| Drum Lock                     | Ratchet                                                                          |
| Guide Arm                     | 4 - Postion                                                                      |
| Material - Coating            | Powder Coating                                                                   |
| Material - Housing            | Steel                                                                            |
| Mounting Style                | Rigid                                                                            |
| Number of Conductors          | 4                                                                                |
| Packaging Type                | Carton                                                                           |
| Primary Cord/Cable Entry      | 1" NPT                                                                           |
| Retraction Weight             | 1.8kg (4.0 lb)                                                                   |
| Wire Size AWG                 | 16                                                                               |
| Electrical                    |                                                                                  |
| Bulb Included                 | N/A                                                                              |
| Cord Type                     | 16/4 SOW                                                                         |
| Current - Maximum per Contact | 8.0A                                                                             |
| GFCI                          | No                                                                               |
| Lamp Type                     | N/A                                                                              |
| Lamp Wattage - Maximum        | N/A                                                                              |
| On/Off Switch                 | N/A                                                                              |
| Voltage - Maximum             | 600V                                                                             |
| Material Info                 |                                                                                  |
| Engineering Number            | 92541N                                                                           |



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Not Reviewed

Not Reviewed

Not Reviewed

Search Parts in this Series

130084 Series

This document was generated on 07/28/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300840138