

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

**Part Number:** [1300850364](#)  
**Status:** **Active**  
**Overview:** [Reels - Woodhead](#)  
**Description:** Woodhead POW-R-MATIC Heavy Duty Cable Reel with Retraction Weight of 7lbs., 12/4 SOW, 24.38m (80.0') Cord Length with Flying Leads

**Documents:**  
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**  
CSA LR29921

**General**  
Product Family Electric Reels  
Series [130085](#)  
Cable Length N/A  
Comments Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.  
Depth 0.58m (22.750")  
Duty Heavy  
Enclosure Rating NEMA 3R  
Height 0.59m (23.38")  
NEMA Configuration N/A  
Overview [Reels - Woodhead](#)  
Product Name POW-R-MATIC  
Type Cable Reel  
UPC 78678879274  
Width 416.10mm (16.38")

**Physical**  
Cable Movement Ratchet Lock  
Cord Length 24.38m (80.0')  
Drum Lock Ratchet  
Guide Arm Option Available  
Material - Coating Powder Coating  
Material - Housing Steel  
Mounting Style Rigid  
Number of Conductors 4  
Packaging Type Carton  
Primary Cord/Cable Entry 1" NPT  
Retraction Weight 3.2kg (7.0 lb)  
Wire Size AWG 12

**Electrical**  
Bulb Included N/A  
Cord Type 12/4 SOW  
Current - Maximum per Contact 14.0A  
GFCI No  
Lamp Type N/A  
Lamp Wattage - Maximum N/A  
On/Off Switch N/A  
Voltage - Maximum 600V

**Material Info**  
Engineering Number 92643



Series image - Reference only

**EU ELV**  
**Not Reviewed**

| <b>EU RoHS</b>                                                | <b>China RoHS</b> |
|---------------------------------------------------------------|-------------------|
| <b>Not Reviewed</b>                                           |                   |
| <b>REACH SVHC</b>                                             |                   |
| Not Reviewed                                                  |                   |
| <b>Halogen-Free</b>                                           |                   |
| <b>Status</b>                                                 |                   |
| <b>Not Reviewed</b>                                           |                   |
| For more information, please visit <a href="#">Contact US</a> |                   |
| China ROHS                                                    | Not Reviewed      |
| ELV                                                           | Not Reviewed      |
| RoHS Phthalates                                               | Not Reviewed      |

**Search Parts in this Series**  
[130085](#) Series

This document was generated on 07/28/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300850364](#)