

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1301430091](#)  
**Status:** **Active**  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Description:** Super-Safeway Cordset 12 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 30.48m (100.0'), NEMA 5-20 125V

**Documents:**  
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

|                               |                                                      |
|-------------------------------|------------------------------------------------------|
| <b>Agency Certification</b>   |                                                      |
| CSA                           | LR6837                                               |
| UL                            | E38085                                               |
| <b>General</b>                |                                                      |
| Product Family                | Wiring Devices                                       |
| Series                        | <a href="#">130143</a>                               |
| IP Rating                     | N/A                                                  |
| NEMA Configuration            | NEMA 5-20                                            |
| Overview                      | <a href="#">Heavy-Duty Industrial Wiring Devices</a> |
| Product Name                  | Super-Safeway                                        |
| Receptacle Type               | Single                                               |
| Specialty                     | N/A                                                  |
| Type                          | Cordset                                              |
| UPC                           | 78678870143                                          |
| <b>Physical</b>               |                                                      |
| Flange                        | No                                                   |
| Flip Lid                      | No                                                   |
| Gender                        | Male-Female                                          |
| Length                        | 30.48m (100.0')                                      |
| Locking Blade                 | No                                                   |
| Poles                         | 2-pole/3-wire                                        |
| <b>Electrical</b>             |                                                      |
| Cord Type                     | 12/3 SOOW                                            |
| Current - Maximum per Contact | 20.0A                                                |
| GFCI                          | No                                                   |
| Lighted Connector             | No                                                   |
| Voltage - Maximum             | 125V                                                 |
| <b>Material Info</b>          |                                                      |
| Engineering Number            | 1433D123                                             |



Series image - Reference only

|                                                               |                   |
|---------------------------------------------------------------|-------------------|
| <b>EU ELV</b><br><b>Not Reviewed</b>                          |                   |
| <b>EU RoHS</b><br><b>Not Reviewed</b>                         | <b>China RoHS</b> |
| <b>REACH SVHC</b><br>Not Reviewed                             |                   |
| <b>Halogen-Free</b><br><b>Status</b><br><b>Not Reviewed</b>   |                   |
| For more information, please visit <a href="#">Contact US</a> |                   |
| China ROHS                                                    | Not Reviewed      |
| ELV                                                           | Not Reviewed      |
| RoHS Phthalates                                               | Not Reviewed      |

**Search Parts in this Series**  
[130143](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301430091