

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300950129

Status:

Active

Overview:

Pulling Grips

Description:

Heavy Duty Wire Mesh Pulling Grip, Double Weave, Rotating Eye, Short Mesh Length 0.635m (25.00"), Approximate Break Strength 12337.71kg (27200 lbs)



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Brochure \(PDF\)](#)

|                             |                              |
|-----------------------------|------------------------------|
| Agency Certification        |                              |
| CSA                         | LR32159                      |
| General                     |                              |
| Product Family              | Cable Grips                  |
| Series                      | 130095                       |
| Eye Type                    | Rotating                     |
| O-Ring                      | N/A                          |
| Overview                    | Pulling Grips                |
| Product Name                | Heavy Duty                   |
| Type                        | Pulling Grip                 |
| UPC                         | 78678835870                  |
| Physical                    |                              |
| Approximate Break Strength  | 12337.71kg (27200 lbs)       |
| Bale Length                 | N/A                          |
| Body Style                  | Straight                     |
| Cable Diameter              | 38.10-50.55mm (1.500-1.990") |
| Color - Grommet             | N/A                          |
| Eye Diameter                | 1 5/8"                       |
| Gender                      | N/A                          |
| Material - Body             | N/A                          |
| Material - Grip             | Galvanized Steel             |
| Mesh Length                 | 0.635m (25.00")              |
| Number of Holes             | N/A                          |
| Thread Size                 | N/A                          |
| Material Info               |                              |
| Engineering Number          | 35870                        |
| Reference - Drawing Numbers |                              |
| Sales Drawing               | SD-130095-106                |

|                                                               |              |
|---------------------------------------------------------------|--------------|
| EU ELV                                                        |              |
| Not Reviewed                                                  |              |
| EU RoHS                                                       | China RoHS   |
| Not Reviewed                                                  |              |
| REACH SVHC                                                    |              |
| Not Reviewed                                                  |              |
| Halogen-Free                                                  |              |
| Status                                                        |              |
| Not Reviewed                                                  |              |
| For more information, please visit <a href="#">Contact US</a> |              |
| China ROHS                                                    | Not Reviewed |
| ELV                                                           | Not Reviewed |
| RoHS Phthalates                                               | Not Reviewed |

Search Parts in this Series

130095 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300950129