

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1301470150](#)  
**Status:** **Active**  
**Overview:** [Watertite Extreme Wet-Location Wiring Solutions](#)  
**Description:** Watertite Extreme Receptacle with Locking Blade, Single Flip Coverplate, 3 Pole/4 Wire, NEMA L16-20 480V, 3ØY

**Documents:**

|                                |                                                      |
|--------------------------------|------------------------------------------------------|
| <a href="#">3D Model</a>       | <a href="#">Brochure (PDF)</a>                       |
| <a href="#">Drawing (PDF)</a>  | <a href="#">RoHS Certificate of Compliance (PDF)</a> |
| <a href="#">3D Model (PDF)</a> |                                                      |

**Agency Certification**

|     |        |
|-----|--------|
| CSA | LR6837 |
| UL  | E68122 |

**General**

|                    |                                                                 |
|--------------------|-----------------------------------------------------------------|
| Product Family     | Wiring Devices                                                  |
| Series             | <a href="#">130147</a>                                          |
| IP Rating          | IP67                                                            |
| NEMA Configuration | NEMA L16-20                                                     |
| Overview           | <a href="#">Watertite Extreme Wet-Location Wiring Solutions</a> |
| Product Name       | Watertite Extreme                                               |
| Receptacle Type    | Single                                                          |
| Specialty          | N/A                                                             |
| Type               | Receptacle                                                      |
| UPC                | 78678871571                                                     |

**Physical**

|               |               |
|---------------|---------------|
| Flange        | No            |
| Flip Lid      | Yes           |
| Gender        | Female        |
| Length        | N/A           |
| Locking Blade | Yes           |
| Net Weight    | 330.668/g     |
| Poles         | 3-pole/4-wire |

**Electrical**

|                               |          |
|-------------------------------|----------|
| Cord Type                     | N/A      |
| Current - Maximum per Contact | 20.0A    |
| GFCI                          | No       |
| Lighted Connector             | No       |
| Voltage - Maximum             | 3ØY 480V |

**Material Info**

|                    |       |
|--------------------|-------|
| Engineering Number | 67W76 |
|--------------------|-------|

**Reference - Drawing Numbers**

|               |                |
|---------------|----------------|
| Sales Drawing | 1301470150-000 |
|---------------|----------------|



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Relevant**

**REACH SVHC**

Not Relevant

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

**China RoHS**

|                 |              |
|-----------------|--------------|
| China ROHS      | Not Relevant |
| ELV             | Not Relevant |
| RoHS Phthalates | Not Relevant |

**Search Parts in this Series**

[130147](#) Series

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301470150 67W76