

6

5

4

3

2

1

E

E

D

D

C

C

B

B

A

A

F3 MAX-LOC NUT

STAINLESS STEEL  
SCREWS W/FLAT  
WASHER 1<sup>1</sup>/<sub>2</sub>"  
AND O-RINGSTAINLESS STEEL  
SCREWS W/LOCK  
WASHER  
(6) REQ'DMAINTAINED ON/OFF  
(505SW-N)

YELLOW BUTTON PILOT LIGHT (505PL-YB)

RED BUTTON PILOT LIGHT (505PL-RB)

BLANK (505BLNK)

GREEN BUTTON PILOT LIGHT (505PL-GB)

E-STOP RED, MAINTAINED (505B-RM)

BLANK (505BLNK)

14.50"

(1.18")  
BETWEEN CENTERS

(3.52" )

STAINLESS STEEL  
SUPPORT RINGS  
(2) REQ'D

(2.31")

## NOTES:

1. INSTALLATION INSTRUCTIONS, BUTTON ID. LABELS. ARE PACK WITH THE PART.
2. ALL BUTTONS ARE HIGH AMBIENT, CHEMICALLY RESISTANT MATERIAL - COLOR BLACK

RELEASE DRAWING EC NO: WNA2011-0412 DRWN: HKNEELAN 2011/02/09 CHKD: HKNEELAN APPR: DTITUS 2011/03/22		DESCRIPTION	QUALITY SYMBOLS <div>▽=0</div> <div>▽C=0</div>	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE NTS	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
					mm	INCH	DRAWN BY HKNEELAN	DATE 2011/02/09	TITLE 5058 W/505SW-N, YELLOW RED & GREEN PILOT BUTTON E-STOP IN POS #7				
				4 PLACES	±--	±--	CHECKED BY HKNEELAN	DATE 2009/02/09					
				3 PLACES	±--	±.005							
A	REV			2 PLACES	±0.13	±0.010	APPROVED BY DTITUS		DATE 2011/03/22	<div>MOLEX</div> MOLEX INCORPORATED			
		1 PLACE			±0.25	±0.020							
		ANGULAR ±1/2°											
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO. 1301260330		DOCUMENT NO. SD-130126-047		SHEET NO. 1 OF 1				
				SIZE A	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301260330