

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1510350003

Status:


Active

Overview:

EXTreme Guardian System

Description:

11.00mm Pitch EXTreme Guardian Power Right-Angle Plug PCB Header, 2.36mm PCB Thickness, Gold Plated, 3 Circuits



Series image - Reference only

Documents:	
3D Model	Packaging Specification PK-151035-0001-001 (PDF)
Drawing (PDF)	Symbol Footprint Data SYM-151035-0003-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-151053-0000-001 (PDF)	

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	151035
Application	Power, Wire-to-Board
Overview	EXTreme Guardian System
Product Name	EXTreme Guardian
UPC	889056047715
Physical	
Breakaway	No
Circuits (Loaded)	3
Circuits (maximum)	3
Durability (mating cycles max)	25
Flammability	94V-0
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	24.845/g
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.86mm
PCB Thickness - Recommended	2.36mm
Packaging Type	Tray
Pitch - Mating Interface	11.00mm
Plating min - Mating	0.076µm
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	80.0A
Voltage - Maximum	600V AC/DC
Solder Process Data	
Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260
Material Info	

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

151035 Series

Mates With

EXTreme Guardian Receptacle Housing

151034

Reference - Drawing Numbers

Packaging Specification	PK-151035-0001-001
Product Specification	PS-151053-0000-001
Sales Drawing	SD-151035-0001-001
Symbol/Footprint Data	SYM-151035-0003-001

This document was generated on 10/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

151035-0003