

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1301490056](#)  
**Status:** **Active**  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Description:** Safeway Flanged Receptacle with Locking Blade, 3 Pole/3 Wire, Non-NEMA 125V/250V

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

|     |        |
|-----|--------|
| CSA | LR6837 |
| UL  | E10176 |

**General**

|                    |                                                      |
|--------------------|------------------------------------------------------|
| Product Family     | Wiring Devices                                       |
| Series             | <a href="#">130149</a>                               |
| IP Rating          | N/A                                                  |
| NEMA Configuration | Non-NEMA Locking                                     |
| Overview           | <a href="#">Heavy-Duty Industrial Wiring Devices</a> |
| Product Name       | Safeway                                              |
| Receptacle Type    | Single                                               |
| Specialty          | N/A                                                  |
| Type               | Receptacle                                           |
| UPC                | 78678802908                                          |

**Physical**

|               |               |
|---------------|---------------|
| Flange        | Yes           |
| Flip Lid      | No            |
| Gender        | Female        |
| Length        | N/A           |
| Locking Blade | Yes           |
| Poles         | 3-pole/3-wire |

**Electrical**

|                               |             |
|-------------------------------|-------------|
| Cord Type                     | N/A         |
| Current - Maximum per Contact | 30.0A       |
| GFCI                          | No          |
| Lighted Connector             | No          |
| Voltage - Maximum             | 125V / 250V |

**Material Info**

|                    |        |
|--------------------|--------|
| Engineering Number | 2908MB |
|--------------------|--------|



Series image - Reference only

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

|                 |              |
|-----------------|--------------|
| China ROHS      | Not Reviewed |
| ELV             | Not Reviewed |
| RoHS Phthalates | Not Reviewed |

**Search Parts in this Series**

[130149](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301490056