

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1729531202

Status:

Active

Overview:

Micro-Fit 3.0™ Connectors

Description:

Micro-Fit\* Terminal Position Assurance (TPA) Retainer, 12 Circuits, 3.00mm Pitch, UL 94V-2, Glow Wire Capable, Black



Documents:

3D Model

Drawing (PDF)

Product Specification PS-43045 (PDF)

Packaging Specification 1729530001-PK-000 (PDF)

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

General	
Product Family	Accessories
Series	172953
Comments	See Product Specification for maximum current rating by circuit size and wire AWG   This Molex product is manufactured from material that has the following ratings, tested by independent agencies:  a) AGlow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.  b) A Glow Wire Flammability Index (GWFI) above 850 deg Cper IEC 60695-2-12 and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire.   The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s).   If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.
Component Type	Terminal Position Assurance
Overview	Micro-Fit 3.0™ Connectors
Product Literature Order No	987651-3501
Product Name	Micro-Fit* TPA, TPA - Term Pos Assurance
UPC	889056430111
Physical	
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Black
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.141/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40°C to +105°C
Material Info	
Reference - Drawing Numbers	
Packaging Specification	1729530001-PK-000
Product Specification	PS-43045
Sales Drawing	SD-172953-002

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
Need more information on product environmental compliance?	
Email <a href="mailto:productcompliance@molex.com">productcompliance@molex.com</a>	
Please visit the <a href="#">Contact Us</a> section for any non-product compliance questions.	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

172953 Series

Use With

Micro-Fit TPA Receptacle Housing Glow Wire Capable 172952

This document was generated on 05/23/2017

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

172953-1202