

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1731090072

Status:

Active

Overview:

FCT D-Sub Connectors

Description:

FCT Standard-Density D-Sub Connector, Male, Straight, Solder Cup, Gold Plating, 500 Mating Cycles, 50 Circuits

Documents:

Product Specification 1727040001-PS-000 (PDF)

Brochure (PDF)

Test Summary 1727040000-TS-000 (PDF)

RoHS Certificate of Compliance (PDF)

Datasheet (PDF)

General

Product Family

D-Sub Products

Series

173109

IP Rating

IP20

Overview

FCT D-Sub Connectors

Product Category

D-Sub Connector

Product Name

FCT Products

Type

Standard Density

UPC

889056319102

Physical

Circuits (Loaded)

50

Circuits (maximum)

50

Color - Resin

White

Durability (mating cycles max)

500

Gender

Male

Material - Contact

Copper Alloy

Material - Resin

PBT

Material - Shell

Steel

Net Weight

17.200/g

Number of Rows

3

Orientation

Straight

PCB Locator

No

PCB Retention

None

Packaging Type

Carton

Panel Mount

Rear

Panel Mount Method

Flange

Pitch - Mating Interface

2.84mm

Pitch - Termination Interface

2.84mm

Plating - Contact

Gold over Nickel

Plating - Shell

Tin

Polarized to Mating Part

Yes

Ports

1

Shielded

Yes

Temperature Range - Operating

-55° to +125°C

Termination Style

Solder Cup

Waterproof / Dustproof

No

Waterproof / Dustproof Type

IP20

Wire Size AWG

20

Electrical

Current - Maximum per Contact

7.5A

Material Info

Engineering Number

F50P0G1

Reference - Drawing Numbers



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

173109 Series

Mates With

FCT Standard-Density D-Sub, Size 5, 50 Position, Socket

This document was generated on 07/30/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

173109-0072