

	12	11		10		9		8		7		6		5		4		3		2		1
LOOSE PIECE		TAPE MOUNTED		SPECIFICATIONS																		
MATERIAL NUMBER	ENGINEERING NUMBER	MATERIAL NUMBER	ENGINEERING NUMBER	STUD SIZE	"S" ±.005 [0.13]	"W" ±.010 [0.25]	"C" MIN.	"L" MAX.	"H"													
190690192	C-101-12	---	---	12	.515 [13.08]	.750 [19.05]	.611 [15.52]	1.280 [32.51]	1.300 [33.02]													
190690195	C-101-14	---	---	14	.265 [6.73]																	
190690196	C-101-38	190690145	C-101-38T	38	.390 [9.91]																	
---	---	---	---	56	.328 [8.33]																	
190690198	C-101-76	190690146	C-101-76T	76	.453 [11.51]	.530 [13.46]	.393 [9.98]	.952 [24.18]	.980 [24.89]													
190690217	C-130-10	190690218	C-130-10T	10	.198 [5.03]																	
190690219	C-130-14	190690221	C-130-14T	14	.265 [6.73]																	
---	---	---	---	38	.390 [9.91]																	
190690223	C-130-56	190690225	C-130-56T	56	.328 [8.33]	.282 [7.16]	.306 [7.77]	.741 [18.82]	.980 [24.89]													
---	---	---	---	4	.119 [3.02]																	
190690230	C-136-06	190690232	C-136-06T	6	.146 [3.71]																	
190690233	C-136-08	190690235	C-136-08T	8	.173 [4.39]																	
190690236	C-140-10	---	---	10	.198 [5.03]	.592 [15.04]	.468 [11.89]	1.056 [26.82]	1.172 [29.77]													
190690238	C-140-14	190690240	C-140-14T	14	.265 [6.73]																	
190690241	C-140-38	190690243	C-140-38T	38	.390 [9.91]																	
190690244	C-140-56	190690246	C-140-56T	56	.328 [8.33]																	
---	---	---	---	209	.209 [5.31]																	
---	---	---	---	413	.413 [10.50]																	

SYMBOLS

⏏ = 0

▽ = 0

▽ = 0

⏏ = 0

▽ = 0

▽ = 0

⏏ = 0

⏏ = 0

⏏ = 0

⏏ = 0

⏏ = 0

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

INCH/MM

SCALE

NTS

GENERAL TOLERANCES (UNLESS SPECIFIED)

MM

INCH

4 PLACES

±

±

3 PLACES

±

± 0.005

2 PLACES

±

0.13

± 0.01

1 PLACE

±

0.25

±

0 PLACES

±

±

ANGULAR TOL

±

0.5 °

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC: MIGRATION TO ECTR/NX

EC NO: 619818

DRWN: ABENJAMINLW

CHK'D: GROJAS01

APPR: JMACNEIL

2019/06/18

2019/06/27

2019/07/10

INITIAL REVISION:

DRWN: EDWIN

APPR: JMACNEIL

1992/02/10

2019/07/10

THIRD ANGLE PROJECTION

DRAWING

C-SIZE

SERIES

19069

RING TONGUE TERMINAL KRIMPTITE 100-SERIES

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER

190690192

DOC TYPE

PSD

DOC PART

000

REVISION

A

MATERIAL NUMBER

CUSTOMER

SHEET NUMBER

SEE TABLE

GENERAL MARKET

1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19069-0523](#)