

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2018410140](#)
Status: **Active**
Overview: [MultiCat Power Connectors with Precision-Machined Contacts](#)
Description: [MultiCat High-Power Inline Receptacle Housing with CPA, 4 Circuits, Black, Key A](#)

Documents:
[3D Model \(PDF\)](#) [Packaging Specification 2018410000-PK-000 \(PDF\)](#)
[3D Model](#) [Test Summary 2018400000-TS-000 \(PDF\)](#)
[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)
[Product Specification 2018400000-PS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification 2018400000-AS-000 \(PDF\)](#)

Agency Certification	
UL	E29179
General	
Product Family	Crimp Housings
Series	201841
Application	Power, Wire-to-Board, Wire-to-Wire
Overview	MultiCat Power Connectors with Precision-Machined Contacts
Product Name	MultiCat
UPC	889056747622
Physical	
Circuits (maximum)	4
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PEI
Net Weight	7.751/g
Number of Rows	1
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	7.40mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +150°C
Material Info	
Engineering Number	2018410140-FCT
Reference - Drawing Numbers	
Application Specification	2018400000-AS-000
Packaging Specification	2018410000-PK-000
Product Specification	2018400000-PS-000
Sales Drawing	2018410000-SD-000
Test Summary	2018400000-TS-000



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per - D(2021)4569-DC (8 July 2021) Halogen-Free Status Low-Halogen For more information, please visit Contact US	China RoHS China ROHS ELV RoHS Phthalates
	Green Image Not Relevant Not Contained

Search Parts in this Series
[201841 Series](#)

Mates With
MultiCat High-Power Inline Plug Housing
[201840](#) . MultiCat High-Power Header
[201843](#) , [201842](#) . MultiCat Cable Assembly
[451420401](#) , [451420410](#)

Use With
MultiCat High-Power Contacts [201846](#) .
MultiCat Female High-Power Pre-Crimped
Lead [797582065](#) , [797582066](#) , [797582067](#) ,
[797582068](#) , [797582069](#) , [797582070](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[201841-0140](#)