

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1704320001](#)
Status: **Active**
Overview: [zQSFP+ and QSFP+ Integrated Product Solutions](#)
Description: [zQuad Small Form Factor Pluggable Plus \(zQSFP+\) Assembly, Surface Mount, 38 Circuits, Gold \(Au\) Plated 0.381µm, Supports QSFP28 / EDR](#)

Documents:

3D Model	Packaging Specification 1704320001-PK-000 (PDF)
3D Model (PDF)	Test Summary TS-170432-0004-001 (PDF)
Drawing (PDF)	Symbol Footprint Data SYM-170432-002-001 (PDF)
Product Specification PS-170432-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-170432-0002-001 (PDF)	

Agency Certification

UL	E29179
----	--------

General

Product Family	I/O Connectors
Series	170432
Application	Board-to-Board, Module-to-Board, Wire-to-Board
Comments	QSFP28 / EDR
Component Type	Receptacle
Electrical Model	Yes
Overview	zQSFP+ and QSFP+ Integrated Product Solutions
Product Name	zQSFP Plus, zQSFP+
Type	N/A
UPC	884982584310

Physical

Circuits (Loaded)	38
Color - Resin	Black
Durability (mating cycles max)	50
Flammability	94V-0
Gender	N/A
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Resin	High Temperature Thermoplastic
Net Weight	2.037/g
Number of Rows	1
Orientation	Right Angle
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Panel Mount	N/A
Pitch - Mating Interface	0.80mm
Plating min - Mating	0.381µm
Polarized to Mating Part	N/A
Ports	1
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	0.5A
Grounding to Panel	Yes
Voltage - Maximum	30V AC (RMS)

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[170432](#) Series

Mates With

[100297](#) zQSFP+ Cable Assemblies, [111040](#) QSFP+ Cable Assemblies, [74763](#) QSFP+ Loopback Adapter

Use With

[111118](#) , [100014](#) zQSFP+ Cage Assemblies

Material Info

Reference - Drawing Numbers

Application Specification	AS-170432-0002-001
Electrical Model Document	1704320004-000, EE-170432-0004-001
Packaging Specification	1704320001-PK-000
Product Specification	PS-170432-001-001
S-Parameter Model	SP-170432-0004-001
Sales Drawing	SD-170432-002-001
Symbol/Footprint Data	SYM-170432-002-001
Test Summary	TS-170432-0004-001

This document was generated on 10/05/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

170432-0001