

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200652260

Status:

Active

Overview:

Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable

Description:

Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 3 Poles, Female (90°) to Pigtail, 22 AWG, Unshielded WSOR Cable, 2.0m (6.56') Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E152210

General

Product Family

Industrial Cordsets

Series

120065

Connector End A

Micro-Change (M12)

Connector End B

Pigtail

IP Rating

IP67

Material - Contact

Brass

Overview

Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable

Product Name

Micro-Change (M12)

Protocol

N/A

Region

Europe

Type

Single Ended

UPC

887191554747

Physical

Cable Diameter

4.80mm (.189")

Cable Length

2.0m (6.56')

Color - Cable Jacket

Black

Coupling Style

Knurled Hexnut, Threaded

Gender

Female-Pigtail

Keyway

Single

LED Indicator

No

Material - Cable Jacket

TPU

Material - Connector Body

TPU

Material - Coupling Nut

Nickel-plated Brass

Material - O-Ring

Fluoro-elastomer

Material - Plating Mating

Gold

Net Weight

123.000/g

Orientation

90° to Pigtail

Poles

3

Temperature Range - Operating

-25°C to +85°C

Wire Size AWG

22

Wire/Cable Type

UL 21215

Electrical

Current - Maximum per Contact

4.0A

Voltage - Maximum

60V

Material Info

Engineering Number

803001B30M020

Reference - Drawing Numbers

Sales Drawing

SD-120065-076-001



Series image - Reference only

EU ELV

Compliant with
Exemption 3

EU RoHS

Compliant with
Exemption 6(c)

China RoHS

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)
Lead

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Compliant with Exemption 3
RoHS Phthalates	Not Contained

Search Parts in this Series

120065 Series

This document was generated on 10/06/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1200652260