

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1733000106

Status:


Active

Overview:

SpeedMezz Connector Family

Description:

SpeedEdge Vertical Receptacle, 0.80mm Pitch, 5.60mm Height, 60 Circuits, UL94V-0, Black



Documents:	
3D Model (PDF)	Packaging Specification PK-70873-6002-001 (PDF)
3D Model	Datasheet (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification 1733000001-000 (PDF)	

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Receptacles
Series	173300
Application	Board-to-Board
Overview	SpeedMezz Connector Family
Product Name	SpeedEdge
UPC	889056733632
Physical	
Circuits (Loaded)	60
Circuits (maximum)	60
Color - Resin	Black
Flammability	94V-0
Glow-Wire Capable	No
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	0.978/g
Number of Rows	2
Orientation	Vertical
PCB Locator	Yes
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount
Unmated Height	5.60mm
Electrical	
Current - Maximum per Contact	1.0A
Voltage - Maximum	250V AC
Material Info	
Reference - Drawing Numbers	
Application Specification	1733000001-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
173300 Series

Mates With
SpeedEdge 60 Circuit Plug 173305-0115

Electrical Model Document
Packaging Specification
S-Parameter Model
Sales Drawing

1733000006-000, 1733000008-000
PK-70873-6002-001
1733000006-000, 1733000008-000
SD-173300-0100-001

This document was generated on 09/30/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[173300-0106](#)